

INDUSTRIAL PRODUCT DATASHEET

RGB USB Camera-100°-720P

RGB USB Camera-100°-720P: Plug-and-play 720P USB camera with 100° wide-angle view and manual focus for robotics vision and prototyping.

SKU

100079619

UPDATED

2026-09-16 02:52:19

PRICE

\$30.00(Excl. VAT)



Overview





The RGB USB Camera-100°-720P delivers premium 720P USB camera performance with a 100° wide-angle view and true plug-and-play UVC compatibility on Windows 7/10/11 and Linux, requiring no drivers. Its precision manual focus from close-up to infinity makes it ideal for robotics training, vision sensing, and wide-area capture with SO-ARM 101 and other robotic arms.

Key Features

- **Unbeatable Value:** Premium 720P USB camera performance at an entry-level price.
- **100° Wide-Angle View:** Broad diagonal FOV eliminates blind spots, perfect for robotics training and wide-area capture.
- **True Plug-and-Play:** UVC-compliant, no drivers needed. Works instantly on Windows 7/10/11 and Linux.
- **Precision Manual Focus:** Sharp focus from close-up to infinity, adaptable to any shooting distance.

Product Gallery



Applications

- Vision Sensing for SO-ARM 101 & Robotic Arms:** Integrate this camera module with SO-ARM 101 or other robotic arms to capture visual environmental data. Gather real-world scene information for your robot vision projects. Plug-and-play UVC compatibility supports multiple operating systems, ideal for robotics prototyping and educational research.

Part List

RGB USB Camera-100°-720P	x1
Connection Cable 2m	x1

Compliance & Logistics

HSCODE	8525891900
USHSCODE	8525895050
UPC	
EUHSCODE	8517600000
COO	CHINA

Resource Links

- <https://www.seeedstudio.com/Camera-Module-OV9732-IMP-100-USB2-0-USB2-0-L38-W38-H16-05mm-p-6982.html>

Seeed Technology Co.,Ltd.

9F, Building G3, International E City,
Zhongshanyuan Road, Nanshan, Shenzhen, China

Tel: +86 0755-80695676

Web: www.seeed.cc

Shop: www.seeedstudio.com