seeed studio

INDUSTRIAL PRODUCT DATASHEET

M12 Fisheye Lens for reCamera - 5MP, 160°

This 1.8mm M12 lens is designed for reCamera applications requiring a wide field of view and flexible image adjustment.

SKU	UPDATED	PRICE
100095034	2026-11-11 09:21:23	$9.90(Excl. VAT)



Overview



This 1.8mm M12 lens is designed for reCamera applications requiring a wide field of view and flexible image adjustment. Featuring manual focus, a bright F1.8 aperture, and support for 1/2.9” image sensors, it delivers clear imaging performance in various lighting conditions while enabling easy screw-and-play installation for rapid integration and deployment.

Key Features

01 **Ultra-wide 1.8mm M12 lens designed for reCamera applications requiring expanded scene coverage and wider field-of-view monitoring.**

02 **Features manual focus adjustment and a bright F1.8 aperture for flexible deployment and clear imaging performance across different lighting conditions.**


03 **M12 Fisheye Lens for reCamera - 5MP, 160°**


04 **M12 Wide Angle Lens for reCamera - 3MP, 140°**

05 **M12 Telephoto Lens for reCamera - 5MP, 20°**

06 **M12 Ultra Telephoto Lens for reCamera - 2MP, 15°**

Product Gallery










Hardware Overview



Resource Links

- https://www.seeedstudio.com/J0018027B-p-6647.html
- M12 Fisheye Lens for reCamera - 5MP, 160° Datasheet
- Resource

Seeed Technology Co.,Ltd.
9F, Building G3, International E City,
Zhongshanyuan Road, Nanshan, Shenzhen, China

Tel: +86 0755-80695676
Web: www.seeed.cc
Shop: www.seeedstudio.com