seeed studio

INDUSTRIAL PRODUCT DATASHEET

Grove - OLED Yellow&Blue Display 0.96 (SSD1315) - SPI/IIC -3.3V/5V

Grove - OLED Yellow&Blue Display 0.96 is built 128*64 resolution with a blue and yellow bi-color display.

SKU	UPDATED	PRICE
104020249	2026-11-11 08:41:43	$5.50(Excl. VAT)



Overview



Grove - OLED Yellow&Blue Display 0.96 is built 128*64 resolution with a blue and yellow bi-color display. It can be light up by either I2C or SPI interface.

Key Features

01 **Low power consumption**

3.3/5V Supply, suitable for many microcontrollers and SBCs

02 **High contrast： Based on SSD1315 it comes in Yellow and Blue colors 128×64 pixels.**

03 **High compatibility**

support I2C and SPI Interface


04 **Easy to use**


compatible with Grove port, just plug-and-play


Product Gallery











Resource Links

- https://www.seeedstudio.com/Grove-OLED-Yellow-Blue-Display-0-96-SSD1315-V1-0-p-5010.html
- SSD1315 datasheet

Seeed Technology Co.,Ltd.
9F, Building G3, International E City,
Zhongshanyuan Road, Nanshan, Shenzhen, China

Tel: +86 0755-80695676
Web: www.seeed.cc
Shop: www.seeedstudio.com