
seeed studio

INDUSTRIAL PRODUCT DATASHEET

Dual P5 32x32 RGB LED Matrix - 160x160mm

Specification： Size:160mmx160mm Module resolution ratio:32x32 Brightness:1600(cd/㎡) Max power consumption:24W Drive mode:1/16 scan Voltage: 5V Port type:HUB75 Weight:0

SKU	UPDATED	PRICE
104990160	2024-08-09 02:02:22	$64.50(Excl. VAT)





Overview




Specification： Size:160mmx160mm Module resolution ratio:32x32 Brightness:1600(cd/㎡) Max power consumption:24W Drive mode:1/16 scan Voltage: 5V Port type:HUB75 Weight:0

Product Gallery







Resource Links

- https://www.seeedstudio.com/Dual-P5-32x32-RGB-LED-Matrix-160x160mm-p-2068.html

Seeed Technology Co.,Ltd.
9F, Building G3, International E City,
Zhongshanyuan Road, Nanshan, Shenzhen, China

Tel: +86 0755-80695676
Web: www.seeed.cc
Shop: www.seeedstudio.com