seeed studio

INDUSTRIAL PRODUCT DATASHEET

WS2813B Digital RGB LED Flexi-Strip 60 LED - 1 Meter

WS2813B Digital RGB LED Flexi-Strip 60 LED - 1 Meter: DC 5V, 18W/meter, WS2813B IC, RGB, 50,000H service life.

SKU	UPDATED	PRICE
104990303	2026-10-23 03:07:08	$7.35(Excl. VAT)



Overview



The WS2813B Digital RGB LED Flexi-Strip 60 LED - 1 Meter operates at DC 5V with a max wattage of 18W/meter and working current of 3.6A/meter. It features WS2813B IC, RGB pixel color, working temperature range -40℃ to 70℃, storage temperature range -50℃ to 80℃, and a service life of 50,000 hours.

Key Features

- Working Voltage: DC 5V
- Working Current:3.6A/meter
- Working Temperature:-40℃ ~ 70℃
- Storage Temperature:-50℃ ~ 80℃
- Max Watt:18W/meter
- IC Size: WS2813B
- Pixel Color: RGB
- Service Life:50,000H

Product Gallery





Compliance & Logistics



HSCODE	9405409000
USHSCODE	8541410000
UPC	841454119593
EUHSCODE	9405413910
COO	CHINA

Resource Links

- https://www.seeedstudio.com/WS2813B-Digital-RGB-LED-Flexi-Strip-60-LED-1-Meter-p-2817.html

Seeed Technology Co.,Ltd.
9F, Building G3, International E City,
Zhongshanyuan Road, Nanshan, Shenzhen, China

Tel: +86 0755-80695676
Web: www.seeed.cc
Shop: www.seeedstudio.com