seeed studio

INDUSTRIAL PRODUCT DATASHEET

RoboMaster M3508 P19 Brushless DC Gear Motor

M3508 P19 Brushless DC Gear Motor is a high-performance servo motor, specially designed for small and medium-sized mobile platforms and robots.

SKU	UPDATED	PRICE
108990061	2025-07-30 07:19:38	$115.00(Excl. VAT)



Overview



M3508 P19 Brushless DC Gear Motor is a high-performance servo motor, specially designed for small and medium-sized mobile platforms and robots. Compared with traditional square wave drive, the M3508 gear motor features sinusoidal drive used with RoboMaster C620 Brushless DC Motor Speed Controller, which boosts higher efficiency, flexibility, and stability. The gear motor's reduction ratio is approximately 19:1.

Product Gallery







Compliance & Logistics

HSCODE	8501310000
USHSCODE	8501316000
UPC	
EUHSCODE	8501109390
COO	CHINA

Resource Links

- https://www.seeedstudio.com/RoboMaster-M3508-P19-Brushless-DC-Gear-Motor-p-2904.html
- RoboMaster C620 Brushless DC Motor Speed Controller V1.01.pdf
- RoboMaster M3508 Accessories Kit V1.0.pdf
- RoboMaster M3508 DC Brushless Gear Motor Mix Control.pdf
- RoboMaster M3508 P19 Brushless DC Gear Motor V1.0.pdf
- RoboMaster M3508 P19 Brushless DC Gear Motor (STEP).zip
- RoboMaster M3508 Accessories Kit (STEP).zip
- RoboMaster C620 Brushless DC Motor Speed Controller (STEP).zip
- takyon driver
- RoboMaster Assistant V1.8

Seeed Technology Co.,Ltd.
9F, Building G3, International E City,
Zhongshanyuan Road, Nanshan, Shenzhen, China

Tel: +86 0755-80695676
Web: www.seeed.cc
Shop: www.seeedstudio.com