seeed studio

INDUSTRIAL PRODUCT DATASHEET

DSCope U3P100 Dual-Channel 1GSa/s Sampling/100Mhz Bandwidth USB3.0 - Portable Oscilloscope

DSCope U3P100 Dual-Channel Portable Oscilloscope with 100MHz bandwidth, up to 1GSa/s sample rate, and USB 3.0.

SKU	UPDATED	PRICE
109060021	2026-10-23 03:05:46	$349.00(Excl. VAT)



Overview




The DSCope U3P100 is a dual-channel portable oscilloscope featuring a 100MHz bandwidth and up to 1GSa/s sample rate. It includes a USB 3.0 interface, up to 2Gbits hardware memory, an ultra-portable unibody aluminum case, and 2 analog channels.

Key Features

- 2 Analog Channels
- USB 3.0 Interface
- 100MHz Bandwidth
- Up to 1GSa/s sample rate
- Up to 2Gbits hardware memory
- Ultra-portable size
- Unibody aluminum case


Product Gallery













Part List

- DSCope U3P100 (fully tested)
- x2 USB 3.0 cable(1.0M length, A to Type-C)
- x2 P6200 probes
- x1 Carrying Case
- Software not included — **download here**

Compliance & Logistics



HSCODE	9030201000
USHSCODE	9030201000
UPC	
EUHSCODE	9030900000
COO	CHINA

Resource Links

- https://www.seeedstudio.com/DSCope-U3P100-Dual-Channel-1GSa-s-Sampling-100Mhz-Bandwidth-USB3-0-Portable-Oscilloscope-p-4517.html
- DSCope U3P100 Datasheet
- DSView User Guide

Seeed Technology Co.,Ltd.
9F, Building G3, International E City,
Zhongshanyuan Road, Nanshan, Shenzhen, China

Tel: +86 0755-80695676
Web: www.seeed.cc
Shop: www.seeedstudio.com