
seeed studio

INDUSTRIAL PRODUCT DATASHEET


Multi Chassis-4WD Robot Kit (ATV version)

The Multi Chassis-4WD Robot Kit (ATV version) is a durable, heavy-load-capable 4WD robot with full metal frame and special texture wheels for sand, lawn, and more.

SKU	UPDATED	PRICE
110990087	2025-07-30 07:08:25	$45.00(Excl. VAT)



Overview



The Multi Chassis-4WD Robot Kit (ATV version) boasts a full metal frame and special texture wheels, making it suitable for heavy loads and traversing sand, lawn, or similar surfaces. It features a strong aluminum alloy chassis and is powered by four DG01D motors with a 48:1 gear ratio, operating at 6V-9V with a nominal current of 800mA.

Key Features

Robot Multi Chassis 4WD kit build with full metal frame and special texture wheel. Benefit by the metal frame and the special wheel, this robot is good for heavy loading, and easy to run on sand, lawn or something else like that.

Features

- Strong and durable Aluminum alloy chassis
- Full metal frame
- Special texture wheel

Specifications

- Size: 178*145*78cm (length*width*height)
- Wheel diameter: Φ78MM
- High-quality ATV wheel (rubber wheel): 4pcs
- DG01D motor 48: 1 ratio gear: 4pcs(Metal output shaft)
- Net weight: 580g
- 5x AAA battery holder
- Supply voltage: 6v-9v
- Nominal current: 800mA
- Stall current: 2800mA

Part List


- 1 x Aluminum chassis top
- 1 x Aluminum chassis bottom
- 4 x DC motor
- 4 x Racing wheel
- 4 x Distance holder M3*25
- 6 x M3*8 flat-head screw
- 4 x M2.5*20 screw
- 4 x M2.5*25 screw
- 4 x M3*22 screw with flange
- 8 x M3*8 screw
- 8 x M2.5 nylon nut
- 2 x M3 nut
- 1 x 5*AA battery holder

- 1 x Spanner (M2.5 & M4)
- 1 x Spanner (M2 & M3)
- 1 x Screw driver

Documents


- Multi Chassis-4WD kit (ATV version) Instruction manual

Product Gallery









Part List

- Size: 178*145*78cm (length*width*height)
- Wheel diameter: Φ78MM
- High-quality ATV wheel (rubber wheel): 4pcs
- DG01D motor 48: 1 ratio gear: 4pcs(Metal output shaft)
- Net weight: 580g
- 5x AAA battery holder
- Supply voltage: 6v-9v
- Nominal current: 800mA
- Stall current: 2800mA
- 1 x Aluminum chassis top
- 1 x Aluminum chassis bottom
- 4 x DC motor
- 4 x Racing wheel
- 4 x Distance holder M3*25
- 6 x M3*8 flat-head screw
- 4 x M2.5*20 screw
- 4 x M2.5*25 screw
- 4 x M3*22 screw with flange
- 8 x M3*8 screw
- 8 x M2.5 nylon nut
- 2 x M3 nut
- 1 x 5*AA battery holder
- 1 x Spanner (M2.5 & M4)
- 1 x Spanner (M2 & M3)
- 1 x Screw driver

Compliance & Logistics

HSCODE	7318160000
UPC	841454105626
COO	CHINA

Resource Links

- https://www.seeedstudio.com/Multi-Chassis-4WD-Robot-Kit-ATV-versio-p-1604.html

Seeed Technology Co.,Ltd.
9F, Building G3, International E City,
Zhongshanyuan Road, Nanshan, Shenzhen, China

Tel: +86 0755-80695676
Web: www.seeed.cc
Shop: www.seeedstudio.com