
seeed studio

INDUSTRIAL PRODUCT DATASHEET

# Sonoff SNZB-03-Zigbee Motion Sensor, Smart home security, Indoor motion detector, Low-cos

Sonoff SNZB-03-Zigbee Motion Sensor, Smart home security, Indoor motion detector, Low-cos: indoor motion detection with eWeLink alerts, 6m/110° range, ZBBridge smart switch control, low battery notification, 3M adhesive install, an...

| SKU | UPDATED | PRICE |
| --- | --- | --- |
| 113991079 | 2026-10-23 02:45:30 | $9.49(Excl. VAT) |



# Overview



The Sonoff SNZB-03-Zigbee Motion Sensor, Smart home security, Indoor motion detector, Low-cos is an indoor motion detector for smart home security that sends instant alert notifications via eWeLink when motion is detected, with a detection range up to 6m and angle up to 110°. It supports intelligent control of home WiFi switches through Sonoff ZBBridge, low battery notifications under 10%, quick 3M adhesive installation, pairing under 30 seconds, and sharing sensor data with family and friends.

# Key Features

- **Motion Detect and Alert:** When the motion sensor is detected, an instant alert notification will be transmitted via eWeLink to your phone.
- **Wide Angle and long-distance:** You can check what is happening in your home by linking the camera. by the sensor, the detection range is up to 6m and the Angle is up to 110°, which can be used for long-distance all-round detection.
- **Intelligent control home switch:** The home WiFi smart switch can be controlled by simply connecting the Sonoff ZBBridge to set the smart scene.
- **Low Energy&Install Automation:** You will receive a notification on the phone when the battery capacity is lower than 10%. 3M Adhesive can install sensors in every corner of the home in a matter of seconds.
- **Friendly human-computer interaction:** When a phone is paired, you can share the page with friends and family and view the sensor data directly.
- **High-Efficiency Pairing:** Efficient matchmaking in less than 30 seconds successfully.

# Product Gallery















## Specification

| Parameter | Description |
|---|---|
| Detection distance | 6M |
| Detection angle | 110° |

| | |
|---|---|
| working temperature | -10℃~40℃ |
| Working humidity | 10%~95RH，non-condensing |
| MCU | CC2530 |
| Dimension | 40×35×28mm |
| Casing material | PC V0 |
| Zigbee Protocol | IEEE 802.15.4 |

# Applications

- **Indoor Smart Home Security**
- **Motion detection**

## Part List

| | |
|---|---|
| Sonoff SNZB-03 | ×1 |
| 3M Adhesive Tape | ×1 |
| User Manual | ×1 |

## Compliance & Logistics

| | |
|---|---|
| HSCODE | 9031499090 |
| USHSCODE | 9031499000 |
| UPC | |
| EUHSCODE | 9013101000 |
| COO | CHINA |

# Resource Links

- https://www.seeedstudio.com/Sonoff-SNZB-03-p-5519.html
- Sonoff-SZNZB-03-Product Specification
- Sonoff-SZNZB-03-User Manual

**Seeed Technology Co.,Ltd.**
9F, Building G3, International E City,
Zhongshanyuan Road, Nanshan, Shenzhen, China

**Tel:** +86 0755-80695676
**Web:** www.seeed.cc
**Shop:** www.seeedstudio.com