seeed studio

INDUSTRIAL PRODUCT DATASHEET

SenseCAP Wireless Barometric Pressure Sensor - LoRaWAN US915MHz

SenseCAP Wireless Barometric Pressure Sensor measures atmospheric pressure, featuring high-precision, stability, and high EMC robustness.

SKU	UPDATED	PRICE
114991733	2026-11-11 10:14:55	$101.00(Excl. VAT)



Overview




SenseCAP Wireless Barometric Pressure Sensor measures atmospheric pressure, featuring high-precision, stability, and high EMC robustness. It's designed with an air pressure sensor, a custom battery, and an industry-grade enclosure, optimized for outdoor use cases that need reliable data collection over years.

Key Features

01 **Rapid installation and deployment (see the video below)**

Product Gallery



Applications

- **Smart Agriculture**
- **Smart Building and Industrial Control**
- **Environmental Monitoring**
- **Other Wireless Sensing Applications**

Resource Links

- https://www.seeedstudio.com/LoRaWAN-Barometric-Pressure-Sensor-US915-p-4310.html
- LoRaWAN Gateway and Wireless Sensor Catalog V1.7
- SenseCAP LoRaWAN Sensor User Manual V1.1
- SenseCAP Product User Guide(LoRaWAN Series) V1.3
- SenseCAP Document Center
- FCC Certificate

Seeed Technology Co.,Ltd.
9F, Building G3, International E City,
Zhongshanyuan Road, Nanshan, Shenzhen, China

Tel: +86 0755-80695676
Web: www.seeed.cc
Shop: www.seeedstudio.com