SGS-CSTC Standards Technical Services (Shanghai) Co., Ltd.

FEDERAL COMMUNICATIONS COMMISSION
Designation Number: CN5033.
Test Firm Registration Number: 479755
NVLAP Lab Code: 201034-0

Verification of Compliance

This Verification of Compliance is granted to below applicant for following designated equipment

VoC No.:	SHEM201201034901ATC
Applicant Name:	BENEWAKE(BEIJING) CO., LTD.
Applicant Address:	10th Floor, Block A, KeShi Building, XinXi Road No. 28(A), HaiDian District,Beijing,China.
Product Name:	DE LiDAR
Model No.:	TF03-100-UART;TF03-180-UART
Test Report Number(s):	SHEM201201034901

Based on tests conducted by SGS-CSTC Standards Technical Services (Shanghai) Co., Ltd. on submitted samples of above mentioned product and found to comply with the technical requirements set out in *ANSI C63.4 & 47 CFR PART 15B regulations for the evaluation of electromagnetic compatibility.*

Please note:
(1) Applicant and/or manufacturer shall fully fulfill FCC SDoC authorization procedure set out in 47 CFR §2.906, §2.909, §2.925, §2.1074, §2.1077.

(2) Applicant and/or manufacturer shall comply additional requirements set out in §15.21, §15.105 and §15.19 to fully comply regulation 47 CFR Part 15.

(3) This VoC is ONLY a conclusion of test result, ONLY serves as technical specifications compliance verification for aforementioned product from SGS Lab.

(4) This verification is only valid for the equipment and configuration described, in conjunction with the test report detailed above.

Parlam Zhan
E&E Section Manager

Date: 2020-12-29

Unless otherwise agreed in writing, this document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at http://www.sgs.com/en/Terms-and-Conditions/Terms-e-Document.aspx. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested and such sample(s) are retained for 30 days only.
Attention: To check the authenticity of testing /inspection report & certificate, please contact us at telephone: (86-755) 8307 1443, or email: CN.Doccheck@sgs.com

NO.588 West Jindu Road,Songjiang District,Shanghai,China 201612 t(86-21)61915666 f(86-21)61915678 www.sgsgroup.com.cn
中国·上海·松江区金都西路588号 邮编: 201612 t(86-21)61915666 f(86-21)61915678 e sgs.china@sgs.com