中国认可
检验
INSPECTION
CNAS IB0078

此报告本年度有效
有效期至2026年12月31日

航 空 运 输 危 险 性 鉴 别 报 告

Identification and Classification Report for Air Transport of Goods

符合DGR锂电池相关包装
说明SECTION II要求

报告编号：
Issued No.: PEKXM202603190191JM720001

生效日期：
Effective Date: 2026.03.19

委托单位：深圳矽递科技股份有限公司

Applicant: Seeed Technology Co.,Ltd

物品名称：智能空间感知助手 W1-B（内置聚合物锂离子电池 CLY403035 3.7V 400mAh 1.48Wh）

Name of Goods: SenseCAP Watcher W1-B (Containing Polymer Lithium Ion Battery CLY403035 3.7 V 400mAh 1.48Wh)

北京迪捷姆空运技术开发有限公司

Beijing DGM Air Transport Technology Development Co.,Ltd.

报 告 书 使 用 约 定
Terms of the Using of the Report

1. 本公司依据本年度国际航协《危险品规则》以及委托人（托运人或其代理人）提供的物品及其运输信息，确定物品的航空运输危险性并出具此报告书。
   The report is issued by DGM China according to IATA ***Dangerous Goods Regulations*** published in the current year and the information of the goods and the information of its shipping provided by the applicant (shipper or his agent).

2. 依据鉴别的需要，本公司要求委托人提供真实、完整的样品及资料。
   According to the demand of identification and classification, DGM China requires the applicant to provide true and exact sample and data of the goods.

3. 委托人保证申报的物品和/或提供的样品与交运的货物是同一种物质。
   The applicant guarantees that the declared goods and/or the sample who provides should be identical with the contents of cargo that is to be transported.

4. 本公司仅对委托方所提供样品的鉴别结果负责。
   DGM China is only responsible for the identification and classification of the sample provided by the applicant.

5. 本报告书经主检员、审核人和批准人签字并加盖本公司印章后生效。
   This report will be effective only after it is signed by the inspector, checker and approver, and stamped by DGM China.

6. 未经本公司书面批准，不得复制本报告书。
   The duplicating of this report is prohibited without the written approval of DGM China.

7. 私自转让、复制、盗用、冒用、涂改、或以任何媒体形式篡改的报告书无效。
   The report is invalid when anything of the following happens - illegal transfer, reproduce, embezzlement, imposture, modification or tampering in any media form.

8. 为适应国际航协《危险品规则》的年度变化，报告书仅在本年度内有效。
   This report is only valid within the year in which the IATA ***Dangerous Goods Regulations*** is effective.

地址：北京首都国际机场货运北路天竺综合保税区BGS货运楼249室　　邮编：101300

电话：010-69479673　　传真：010-69479621

网址：www.dgmchina.com.cn　　E-mail: test@dgmchina.com.cn

项目编号 Item No.		PEKXM202603190191	签发日期 Issued Date	2026.03.19
鉴别目的 Identification Purpose		是否属于航空运输危险物品 Dangerous Goods or not restricted	鉴别日期 Identification Date	2026.03.19
鉴别依据 Identification Criteria		IATA DGR 67th, 2026		
物品名称 Name of Goods	中文 Chinese	智能空间感知助手 W1-B（内置聚合物锂离子电池 CLY403035 3.7V 400mAh 1.48Wh）		
	英文 English	SenseCAP Watcher W1-B (Containing Polymer Lithium Ion Battery CLY403035 3.7V 400mAh 1.48 Wh)		
生产厂家 Manufacturer		深圳市超力扬科技发展有限公司 SHENZHEN CHAOLIYANG TECHNOLOGY DEVELOPMENT CO., LTD.		
件数 Pieces			托运人或托运人代理人声明 本人（本单位）声明：上述运输信息填写真实、准确，鉴别报告已获得委托单位的授权使用，实际运输的货物情况与本鉴别报告一致。如因信息填写错误、实际运输的货物情况与本鉴别报告不一致造成的一切后果，由本人（本单位）承担全部责任，并赔偿对承运人造成的全部损失。 托运人或托运人代理人签字： 盖章：	
运单号 Air waybill No.				
目的港 Destination				
物品信息 Nature of the goods		该样品为银色近长方体电池。 型号：CLY403035 尺寸：36.3mm×29.6mm×3.7mm 每包装件中电池/电芯数量：45 每包装件中电池/电芯净重：0.387kg 该电池属于单芯锂电池。该锂电池不属于召回电池，不属于废弃和回收电池，并按照DGR3.9.2.6.1(e)规定的质量体系进行制造。装有电池（或电芯）的包装件或完整的包装件经评估，能满足3m堆码试验的要求。 该设备已经做好防意外启动措施。该电池安装在智能空间感知助手上，每台智能空间感知助手含电池一块。单个电池样品重量：8.6g。 This sample is silver almost cuboid battery. Model: CLY403035 Size: 36.3mm×29.6mm×3.7mm Number of batteries / cells per package: 45 Net quantity of batteries/cells per package: 0.387kg The batteries belong to single cell lithium batteries. The lithium batteries don't belong to batteries returned to the manufacturer for safety reasons, are not waste lithium batteries and not lithium batteries being shipped for recycling or disposal, are manufactured under a quality management program as described in 3.9.2.6.1(e). Each package of cells or batteries or the completed package has been assessment, is capable of withstanding force applied to the top surface for a duration of 24 hours, equivalent to the total mass of identical packages if stacked to a height of 3m(including the sample).		

项目编号 Item No.		PEKXM202603190191
物品名称 Name of Goods	中文 Chinese	智能空间感知助手 W1-B（内置聚合物锂离子电池 CLY403035 3.7V 400mAh 1.48Wh）
	英文 English	SenseCAP Watcher W1-B (Containing Polymer Lithium Ion Battery CLY403035 3.7V 400mAh 1.48 Wh)
鉴别结论 Conclusions		该物品为锂离子/聚合物电池，安装在设备上。额定瓦特小时为1.48Wh。已通过 UN38.3 测试，每个包装件上均有电池标记。 根据IATA DGR，锂离子电池符合包装说明967第II部分。 This goods is lithium ion/polymer battery, contained in equipment. Watt-hour rating is 1.48Wh. Each battery is of a type proved to meet the Requirements of each test in the UN MANUAL OF TESTS AND CRITERIA, Part III, sub-section 38.3, Each package is marked with battery mark. According to IATA DGR, lithium ion batteries in compliance with Section II of PI 967.

运输危险性建议 Suggestion for Transport				
	UN/ID 编号 UN/ID No.	运输专用名称 Proper Shipping Name	类或项 Class or Div. (次要危险性) (Subsidiary Risk)	包装等级 Packing Group
	/	/	/	/
	包装说明 Packing Inst.	客货机 Passenger and Cargo Aircraft	/	
		仅限货机 Cargo Aircraft only	/	
	注意事项 Remarks	电池或电芯必须加以保护，防止短路. 设备必须采取措施防止意外启动. Batteries or cells must be protected so as to prevent short circuits, and the equipment must be equipped with an effective means of preventing accidental activation.		

主检员 Prepared by: 纪靖娟

审核人 Checked by: 李超平

批准人 Approved by:

报告单位（盖章） Stamp

北京迪捷姆空运技术开发有限公司 DGM-CHINA

制单： 纪靖娟03


智能空间感知助手 W1-B（内置聚合物锂离子电池 CLY403035 3.7V 400mAh 1.48Wh）


PEKXM202603190191














锂电池/钠离子电池 UN38.3 试验概要 Test Summary

项目编号：PEKXM202603190191

单位信息 Company Information	
委托单位 Consignor	深圳矽递科技股份有限公司/Seeed Technology Co.,Ltd 深圳市南山区西丽街道中山园路 1001 号 TCL 国际 E 城 G3 栋 9 楼/9F, Building G3, TCL International E City, Zhongshanyuan Road, Nanshan, Shenzhen
生产单位 Manufacturer	深圳市超力扬科技发展有限公司/SHENZHEN CHAOLIYANG TECHNOLOGY DEVELOPMENT CO., LTD. 深圳市宝安区西乡街道劳动社区西乡大道 288 号华丰总部经济大厦 D 座 623/623, Block D, Huafeng Headquarters Economic Building, No. 288 Xixiang Avenue, Labor/Community, Xixiang Street, Bao'an District, Shenzhen city, Guangdong, P.R. China 电话/Tel：+86-755-29558690　邮箱/Mail：chaoliyang@foxmail.com　网址/Website：http:// www.chaoliyang.com
测试单位 Test Lab	众检检验认证（深圳）有限公司/CMC Testing International (Shenzhen) Co., Ltd. 中国广东省深圳市宝安区福海街道和平社区荔园路恺辉茂工业园厂房 B 栋 101、104 /101&104, Building B, Kaihuimao Industrial Park, Liyuan Road, Heping Community, Fuhai Street, Baoan District, Shenzhen, Guangdong, China 电话/Tel：400-1668-320　邮箱/Mail：nfo@cmczj-lab.com 网址/Website：http://www.cmczj-lab.com

电池信息 Battery Information			
名称 Name	聚合物锂离子电池 Polymer Lithium Ion Battery	电池/电芯类别 Battery/Cell Classification	单电芯锂离子电池 Single Cell Li-ion Battery
型号 Type	CLY403035	商标 Trademark	/
额定电压 Normal Voltage	3.7V	额定容量 Rated Capacity	400mAh
额定能量 Watt-hour rating	1.48Wh	外观/Appearance	银色近长方体 Approximate Silver Cuboid
质量/Mass	8.6g	锂含量/Li Content	不适用 N/A

测试信息 Test Information			
测试报告编号 Test Report Number	CMC240529021	测试报告签发日期 Date of Test Report	2024-07-22
测试标准 Edition of UN Manual of Tests and Criteria Used	联合国《试验和标准手册》（第 7 版修订 1）38.3 节 UN "Manual of Tests and Criteria" ST/SG/AC.10/11/Rev.7/Amend1/Subsection 38.3		

T.1：高度模拟 Altitude Simulation	通过 Pass	T.2：温度试验 Thermal Test	通过 Pass	T.3：振动 Vibration	通过 Pass
T.4：冲击 Shock	通过 Pass	T.5：外部短路 External Short Circuit	通过 Pass	T.6：撞击/挤压 Impact/Crush	通过 Pass
T.7：过度充电 Overcharge	通过 Pass	T.8：强制放电 Forced Discharge	通过 Pass	/	
UN38.3.3.1(f)或/or UN38.3.3.2(d)	不适用 N/A		UN38.3.3.1(g)或/or UN38.3.3.2(e)	不适用 N/A	
备注 Note	/				
签名 Signatory 职务 Title	检验员		签发日期 Issued Date	2026-03-19	