


SenseCAP IP68 Waterproof Junction Box





| Technical data | | |
|---|--|-----------|
| Model | Junction-Box-Kit | |
| Material | Housing | Conductor |
| | PC | Brass |
| Rated power | 24A 450VAC | |
| IP code | IP68 | |
| Working temperature | T105 | |
| Rated connecting capacity | 0.5 ~2.5mm ² | |
| Available cable diameter (Rubber cable) | 4-8mm | |
| Waterproof test | 10M 150hours | |
| Product size | 130.14mm*80.5mm*35.3mm (Refer to actual drawing) | |
| Certification | KEMA,ENEC,CE,UKCA,CB,SAA,ROHS | |

Dimension



SECTION A-A



Product breakdown

