HT-1006 50 Ohm ATTENUTOR SPECIFICATIONS

Customer:
Smp.NO:
Product NO:

PICTURE



Label

HT-1006 10dB
6GHz / 2w

◆ **MECHANICAL SPECIFICATIONS**

ITEM	DESCRIPTION	UNIT
Housing	Stainless Steel	
Connector	50Ω, Male & Female SMA	
Connector Screw Thread	W 1/4"-36UNF	inch
Dimensions	9.35(ϕ)×30	mm
Net Weight	8	g

◆ **ELECTRICAL SPECIFCATIONS**

ITEM	MIN	TYP	MAX	UNIT
Frequency Range		0.3～6000		**MHz**
Impedance		50		Ω
Insertion Loss (0.3～6000 MHz)		±0.35	±0.5	dB
In/Out Return Loss (0.3～6000 MHz)	18			dB
In/Out VSWR (0.3～6000 MHz)			1.29	
Power Rating		1.0	2.0	W

CUSTOMER	REVIEW RESULT	APPROVE	ENGINEER	PREVIEW	PAGE/TOTAL
	OK	----------	----------	V.00	1/2

HT-1006

Insertion Loss and In/Out Return Loss

Span:6000MHz




Fig.1

CUSTOMER	REVIEW RESULT	APPROVE	ENGINEER	PREVIEW	PAGE/TOTAL
	OK	----------	----------	V.00	2/2