


Grove Female Header Datasheet

Port A: 2.0 – 4A Right-Angle Pin



Technical Specifications

- Pitch: 2.0 mm
- Number of Positions: 4
- Applicable Wire Gauge: AWG22 – 28
- Rated Voltage: 100 V AC/DC
- Rated Current: 1.5 A
- Withstanding Voltage: 500 V AC / 1 minute
- Operating Temperature: –25 °C to +85 °C
- Materials:
 1. Housing: Nylon 66
 2. Contacts (Pins): Brass

Note: Unspecified tolerance $\pm 0.5\text{MM}$

Packaging: 10 pcs per 8 x 12 Anti-Static bag