

## 二、外观结构




由 Autodesk 教育版产品制作

由 Autodesk 教育版产品制作

ROHS

Connector  
24Pins Description

NO.	NAME
01	NC
02	AGND
03	SIO_D
04	AVDD_
05	SIO_C
06	RESET
07	VSync
08	PWDN
09	HS(Href)
10	DVDD_
11	DOVDD_
12	D7
13	MCLK
14	D6
15	GND
16	D5
17	PCLK
18	D4
19	D0
20	D3
21	D1
22	D2
23	NC
24	NC



Lens Parameters	5P+650nm IR	Elec. Parameters	OV3660@1/5"
EFL(mm)	1.63mm±5%	Array Size	2048*1536@15fps
Aperture(f/No.)	2.2±5%	Analog(AVDD)	2.5v~3.0v
Field of View(°)	D=102° H=85°	In/Output(DOVDD)	1.8v/2.8v
TV Distortion(%)	< 8%	Core/Digital(DVDD)	1.5v
Chief of Ray Angle(°)	< 30°	Chief of Ray Angle(°)	< 27.6°

TITLE :		SCALE :	
UNSPECIFIED TOL :		PROJECT NO. :	
XX ± 0.05	CHK BY :	MTZ	20 / 12 / 2016
XX ± 0.05	CHK BY :	Matthew	
X ± 0.1	APP BY :	Buyer	
L ± 0.05	APP BY :	Buyer	
ALL DIMENSION IN MM		REMOVE ALL BURS	DO NOT SCALE
		BREAK SHARP EDGES	SHEET OF
			P1/1
			A4

由 Autodesk 教育版产品制作

由 Autodesk 教育版产品制作