

INDUSTRIAL PRODUCT DATASHEET

# Feetech ST3215 C044 Servo

## 7.4V 1:191 Gear Ratio

Feetech ST3215 C044 Servo: 7.4V, 1:191 gear ratio, high-precision positioning, real-time feedback, overload protection, used on leader arm.

| SKU       | UPDATED             | PRICE              |
|-----------|---------------------|--------------------|
| 101090141 | 2026-07-27 03:35:56 | \$20.00(Excl. VAT) |



# Overview



The Feetech ST3215 C044 Servo offers 360-degree positioning with precise angle control, multi-turn continuous rotation capability, and real-time feedback of position, speed, voltage, current, temperature, and load. It includes a 1:191 gear reduction ratio metal gearbox, overload and overcurrent protection, and is used on a leader arm.


# Key Features

---

## **[Note]**

- From China warehouse to the United States, choose "**US Direct Group Shipping**" to enjoy duty-free !
- **High Precision** Provides 360-degree positioning with precise angle control and multi-turn continuous rotation capability
- **Metal Gearbox** Includes 1:191 gear reduction ratio metal gearbox
- **Easy Calibration** Offers one-touch midpoint calibration
- **Rich output** Provides real-time feedback of position, speed, voltage, current, temperature, and load
- **Overload protection** Provides overload and overcurrent protection

# Product Gallery





## Specification

|                       |                     |
|-----------------------|---------------------|
| Product               | Feetech ST3215 C044 |
| Voltage               | 5- 8.4V             |
| Operating Temperature | -20°C~60°C          |

|                         |                        |
|-------------------------|------------------------|
| Mechanical Dimension    | 45.2mm x 24.7mm x 35mm |
| Communication Interface | Serial                 |

# Hardware Overview



# Applications

- Used on leader arm

## Part List

|                   |     |
|-------------------|-----|
| ST3215-C044 Servo | x1  |
| Servo Horn        | x2  |
| Screw             | x18 |
| JST Wire          | x1  |

## Compliance & Logistics

|          |            |
|----------|------------|
| HSCODE   | 8501109990 |
| USHSCODE | 8501106080 |
| UPC      |            |
| EUHSCODE | 8501109390 |
| COO      | CHINA      |

# Resource Links

- <https://www.seeedstudio.com/Feetech-ST-3215-C044-Heavy-Duty-Servo-7-4V-1-191-Gear-Reduction-p-6460.html>
- [Datasheet](#)
- [Github](#)
- [Debug Software](#)
- [Modbus-RTU Protocol](#)

**Seeed Technology Co.,Ltd.**  
9F, Building G3, International E City,  
Zhongshanyuan Road, Nanshan, Shenzhen, China

**Tel:** +86 0755-80695676  
**Web:** [www.seeed.cc](http://www.seeed.cc)  
**Shop:** [www.seeedstudio.com](http://www.seeedstudio.com)