seeed studio

INDUSTRIAL PRODUCT DATASHEET

Yeelight SunFlower

Wireless smart LED scene lighting with app control and extendable plug-and-play design.

SKU	UPDATED	PRICE
104060005	2024-08-09 02:28:52	$125.00(Excl. VAT)



Overview



The Yeelight SunFlower is a wireless smart scene lighting system that integrates into your home Wi-Fi network for seamless control. It enables smart device-based adjustment of color and brightness, with scene saving for instant recall.

Key Features

Yeelight sunflower is a wireless, smart, scene lighting system. It can be installed into your home Wi-Fi network, and all the bulbs form a system with control box automatically. You may control the bulb to change their color and brightness with smart device such as smart phone or pad, also you may save the setting to a scene and recall it at next time. Now the app supports iOS version 5.0+ and Android 2.3.3+.

Starter Pack

For the starter pack, there are 3 yeelight bulbs and 1 control box; it is the base lighting system.

1) The Bulb

The yeelight sunflower bulb is a LED lighting bulb, in which there is a wireless sending/receiving component working via Zigbee signals. The bulb receives signals from control box and changes color and brightness to what you want.

2) Control box

The control box is a LAN (local area network) to Zigbee Bridge, which transforms the smart phone control commands (Wi-Fi signals) to Zigbee signals. The control box has one LAN socket, with which it can be connected to your home Wi-Fi AP. When it boots up, an IP address will be assigned and your smart phone can search and connect to it via Wi-Fi. The following figure shows the interfaces on control box.

Features

- Intelligent, wireless scene lighting
- Featuring a wireless smart network: just plug and play
- Extendable via single packs

Specifications

- Product Name Yeelight Sunflower
- Diameter 50mm
- Height 104mm
- Weight 155g (excluding packing) *
- Wattage 6W
- Standby Power Less than 0.3W
- Certifications CCC, FCC, CE (in progress)
- Color Temperature 6500K White + RGB
- Dimming Software dimming
- Control Range 30m
- Supported Devices iOS 5+, Android 2.3+
- Excepted lifetime More than 20,000 hours
- Voltage AC 110-240-V 50/60Hz

- Limitations Can not be used in closed spaces or outdoors
- Warranty 1 Year
- Packing Dimensions 300mm x 240mm x 65mm
- Base Interface E27

Part List

- 3 x LED bulb
- 1 x Control box
- 1 x Network cable
- 1 x Power adapter
- 1 x USB power cable

NOTE: It is Chinese Standard power adapter within the product. If you want Europe Standard one, we advise **Europe Standard USB Wall Power Supply** for you.

Document

- **APP for iOS**
- **APP for Android**
- **User Manual**
- **Welcome Guide**
- **Sunflower API**

Any further questions for technical support, please contact **support@yeelight.com**. See more information about Yeelight on the **official website**.

Product Gallery







Part List

Yeelight SunFlower	1

Compliance & Logistics

HSCODE

Resource Links

- https://www.seeedstudio.com/Yeelight-SunFlower-p-1940.html

Seeed Technology Co.,Ltd.
9F, Building G3, International E City,
Zhongshanyuan Road, Nanshan, Shenzhen, China

Tel: +86 0755-80695676
Web: www.seeed.cc
Shop: www.seeedstudio.com