seeed studio

INDUSTRIAL PRODUCT DATASHEET

Dual Core Mini PC MK808

Turn any HDMI display into a smart entertainment system with the Dual Core Mini PC MK808, featuring a 1.6 GHz dual-core processor, Android 4.1, Wi-Fi, Bluetooth, and expandable storage.

SKU	UPDATED	PRICE
113990004	2024-08-09 02:09:58	$49.00(Excl. VAT)



Overview



The MK808 is a compact Android 4.1 device that plugs into a TV or monitor via HDMI to run apps, watch movies, stream videos, play games, and browse the web on a big screen. It features a dual-core 1.6 GHz CPU, 1 GB RAM, 8 GB onboard storage, Wi-Fi 802.11 b/g/n, Bluetooth 4.0, USB OTG/host, a TF card slot (up to 32 GB), and plug-and-play simplicity with low heat dissipation.

Key Features

MK808 is designed to be plugged into a TV or a monitor via HDMI, allowing you to run Android apps on a big screen. You can connect a keyboard, mouse, game pad, or other accessories and watch movies, stream videos from the internet, play games, surf the web, or check your email.

Features

- Plug and play
- Compact and low heat dissipation
- Standard USB support USB mouse & keyboard
- Mini USB support OTG/HOST
- TF card slot

Specifications

- CPU: Rk3066 Dual Core 1.6(Cortex - A9)
- Ram: DDR3 1GB
- Rom: On board NAND Flash 8G
- Expand Micro SD: T-Flash(Maximum support 32GB)
- Video Format: WMV/ASF/MP4/3GP/3GM4V/AVI/MJPEG/RV10/DivX/VC-1/MPEG-2/MPEG-4/H.263/H.264/1280*720P HD 30fps, 1080P/720*480 D1 30fps
- Audio Format: Support MP3/WMA/APE/FLAC/ACC/OGG/AC3/WAV
- Picture Format: Support Max.8000*8000 JPEG BMP GIF PNG
- WIFI: Support 802.11 b/g/n
- Bluetooth: Support Bluetooth V4.0
- Output: MINI HDMI Port
- OS: Google Android 4.1(Flash 11.X; HTML5)
- Dimension: 88mm*31.5mm*15.8mm
- Wight： 〈50g
- Working environment: 5℃-35℃, 30%-90% Humidity
- Storage environment: -20℃-60℃, 10%-90% Humidity

Interfaces

- 1*Mini USB support OTG/HOST(USB port RJ45)
- 1*Standard USB support USB mouse & keyboard
- 1*MINI USB for charging
- 1*TF card slot
- 1*Blue LED(When connect to power)
- 1*Physical button for upgrading software

Product & Accessories

- MINI TV Dongle
- HDMI extention Wire

- USB Power Supply Wire
- Adapter
- User Manual

Product Gallery





Compliance & Logistics

HSCODE

Resource Links

- https://www.seeedstudio.com/Dual-Core-Mini-PC-MK808-p-1421.html

Seeed Technology Co.,Ltd.
9F, Building G3, International E City,
Zhongshanyuan Road, Nanshan, Shenzhen, China

Tel: +86 0755-80695676
Web: www.seeed.cc
Shop: www.seeedstudio.com