
seeed studio

INDUSTRIAL PRODUCT DATASHEET


Desktop 3D printer G150 (150*150*150mm)

G150 Desktop 3D Printer: reliable FDM prototyping with a 150 mm^3 build volume and intuitive Cura-based operation.

SKU	UPDATED	PRICE
114991766	2024-08-09 02:30:48	$699.00(Excl. VAT)



Overview



The G150 3D Desktop Printer is a compact FDM printer with a 150×150×150 mm build volume, suitable for personal projects and commercial prototyping. It offers a full-colour touch screen, Cura software compatibility, and supports PLA/ABS filaments with layer thicknesses from 0.05–0.2 mm.

Key Features

Description

If you would like to purchase or obtain more information about this item, please email us at: Manufacturing@chaihuo.org

-

• The G150 3D Desktop Printer is our most popular 3D printers where it can be used for personal interest projects all the way to prototypes for commercial projects by providing an easy to use and reliable prototyping experience.

• G150 also facilitates with Cura, the open-source 3D printing software, allowing 3D models to be printed out using 3D printers with ease. On top of that, Cura has built a large **user community** which are very useful for frontend support.

Product Features:

• **Moulding Method:** FDM

• **Software Language:** English/Chinese

• **LCD Screen:** Full Colour Touch Screen

• **Printing Precision(mm):** 0.05-0.2

• **Moulding Size(mm):** 150*150*150

• **Layer Thickness(mm):** 0.05-0.2

• **Nozzle Temperature:** 0-235℃

• **Moving Speed:** 200-500mm/s

• **Positioning Precision(mm):** X/Y axis: 11μ; Z axis: 2.5μ

• **Build Plate Temperature:** Professional build plates do not require heating

• **Filaments:** PLA/ABS

• **Input Voltage/Frequency/Current/Power:** 220V, 50-60HZ, 5.4A/2.2A, 350W

• **Filament Diameter(mm):** 1.75

• **Interface Type:** USB/SD Card

• **Frame:** Metal

• **Operator Interface:** LCD

• **File Format:** STL/OBJ


• **Environment: Temperature:** 15-32℃, Humidity 20-50%

• **Quality Certificates:** CE,FCC,ROHS

Technical Details


TECHNICAL PARAMETERS

Product Gallery











Resource Links

- https://www.seeedstudio.com/Desktop-3D-printer-G150-p-2882.html

Seeed Technology Co.,Ltd.
9F, Building G3, International E City,
Zhongshanyuan Road, Nanshan, Shenzhen, China

Tel: +86 0755-80695676
Web: www.seeed.cc
Shop: www.seeedstudio.com