seeed studio

INDUSTRIAL PRODUCT DATASHEET

Rubber Duck 5.8Ghz SMA Articulated Antenna

Rubber Duck 5.8Ghz SMA Articulated Antenna: a 5.8GHz omnidirectional antenna for WiFi, Wireless Video, and FPV, included with select RF Explorer models.

SKU	UPDATED	PRICE
318020021	2026-10-23 03:12:08	$6.95(Excl. VAT)



Overview



The Rubber Duck 5.8Ghz SMA Articulated Antenna is a 5.8GHz rubber duck omnidirectional antenna ideal for WiFi, Wireless Video, and FPV use. It is the same antenna included in several RF Explorer models, including the 6G and 6G Combo, and can serve as a replacement or extra antenna.

Key Features

- Rubber duck 5.8GHz perfect for WiFi, Wireless Video, FPV
- Same antenna included in several RF Explorer models

Description

The 5.8Ghz rubber duck omnidirectional antenna is the perfect choice to use RF Explorer in 5.8GHz bands. It also has moderate quality reception at 2.4GHz band and therefore can be used as multi-band antenna.

This antenna is included in several RF Explorer models such as 6G and 6G Combo. You can order this as replacement if your original antenna got damaged or lost, or as an extra antenna for multiple purposes such as using it with RF Explorer Signal Generator.

Specification

Part List

1 x Rubber duck 5.8Ghz antenna

Documents

Designer Website: www.rf-explorer.com

For technical support or questions, please visit our **website**.

Product Gallery











Specification

Impedance	50ohm
Connector	SMA male
Type	rubber duck articulated

Characterized Response	5700-5800MHz (usable at 2.4GHz but not characterized)
VSWR	<2.0
Polarization	vertical
Gain	up to 2dBi
Max power	50W

Part List

Impedance	50ohm
Connector	SMA male
Type	rubber duck articulated
Characterized Response	5700-5800MHz (usable at 2.4GHz but not characterized)
VSWR	<2.0
Polarization	vertical
Gain	up to 2dBi
Max power	50W

Compliance & Logistics



HSCODE	9030900090
USHSCODE	9030904600
UPC	841454118657
EUHSCODE	9030900000
COO	CHINA

Resource Links

- https://www.seeedstudio.com/Rubber-Duck-5-8Ghz-SMA-Articulated-Antenna-p-2667.html

Seeed Technology Co.,Ltd.
9F, Building G3, International E City,
Zhongshanyuan Road, Nanshan, Shenzhen, China

Tel: +86 0755-80695676
Web: www.seeed.cc
Shop: www.seeedstudio.com