

INDUSTRIAL PRODUCT DATASHEET

reComputer Industrial R2135-12 - The Most Reliable and Powerful Raspberry Pi Edge AI/IOT Controller

The reComputer Industrial R2135-12: the most reliable and powerful Raspberry Pi edge AI/IoT controller with CM5 performance, AI acceleration, and industrial-grade connectivity.

SKU

100061305

UPDATED

2026-04-30 08:59:33

PRICE

\$509.00(Excl. VAT)



Overview



The reComputer Industrial R2135-12 is a rugged edge AI/IoT controller powered by Raspberry Pi CM5, offering up to 16GB RAM, 32GB eMMC, and optional Hailo-8 AI acceleration up to 26 TOPS. With fanless cooling for -20–65°C operation, isolated digital I/O (RS485, RS232, CAN FD, DI, DO), and versatile wired/wireless connectivity, it excels in industrial automation, AI vision, smart transportation, and building management.

Key Features

Note:

- Options marked with * require additional purchase according to the **bundle**.
- For 4G functionality, both a 4G module and a 4G antenna must be selected.
- For GPS functionality, both a 4G module and a GPS antenna must be selected.
- For LoRaWAN® functionality, LoRaWAN® module must be selected.
- **Price Increase Announcement**
Date: March 2, 2026
Due to increased demand for modules and SSDs, reComputer' pricing is expected to rise by approximately \$20-\$80 in the coming weeks. Please confirm your orders and requirements accordingly to help secure availability.
- **Powerful Performance with Raspberry Pi CM5:** Broadcom BCM2712 quad-core Arm Cortex-A76 64-bit SoC @ 2.4GHz. Features up to 16GB RAM and 32GB eMMC.
- **Robust Heat Dissipation:** High-performance fanless cooling, engineered to handle the intense heat of AI workloads and ensure stable operation from -20°C to 65°C.
- **Industrial-Grade Reliability:** High Accuracy RTC, hardware watchdog and optional UPS supercapacitor. Optional TPM/ATECC608A. IP40, aluminum alloy enclosure provides industrial-grade protection. Supports DIN-rail and wall mounting. Guaranteed production until at least December 2036.
- **AI-Optimized Computing:** With the optional Hailo-8 AI accelerator, it delivers up to 26 TOPS, enabling real-time, high-performance AI vision processing across multiple channels.
- **Rich Industrial Connectivity:** 2x RS485, 2x RS232, 2x CAN FD, 4x DI, 4x DO, all isolated. 1x 10M/100M/1000M Ethernet (PoE), 1x 10M/100M Ethernet. 2x HDMI 2.0. 3x Type-A USB3.0, 1x Type-A USB2.0, 1x Type-C USB2.0 (for OS update). 1x Nano SIM card slot.
- **Versatile Wireless Connectivity:** On chip Wi-Fi and BLE. Flexible expansion via Mini-PCIe for LTE, LoRa®, Zigbee. M.2 B-Key for 4G/5G.


Seeed Studio Tutorial of AI Kit with Raspberry Pi: From Zero to Hero

This course is designed to teach you how to harness the power of AI on the Raspberry Pi, with a focus on using an AI kit to perform computer vision tasks. You'll learn how to integrate AI into real-world IoT applications, from object detection and image classification to more complex visual recognition tasks.

We will guide you step-by-step through setting up your Raspberry Pi, using AI frameworks, and deploying these models in various practical scenarios.

Product Gallery






Specification

Hardware Specification		
Product Series	R21xx-12	R21xx-10
CPU	Raspberry Pi Compute Module 5, 2.4GHz quad-core 64-bit Arm Cortex-A76	
AI Processor	1x Pre-installed Hailo-8 M.2 AI Acceleration, 26TOPS	*
Operating System	Raspbian, Debian	
Memory & Storage	2GB/4GB/8GB/16GB RAM, 16GB/32GB/64GB eMMC	
System Specification		
Power Input	DC 9V~36V, 2-pin Terminal Block	
PoE(as powered device)	IEEE 802.3 at Standard 25.5W PoE	
Power Switch	No	
Reboot Switch	Yes	
Interface		
Ethernet & USB	1x 10/100/1000 Mbps(supports PoE PD); 1x 10/100 Mbps IEEE 802.3/802.3u	
	3x USB-A 3.0 Host; 1x USB-A 2.0 Host; 1x USB-C 2.0 (For flashing OS & Debug)	
COM and I/O	2x RS485(Isolated); 2x RS232(Isolated); 2x CAN FD(Isolated)	
	4x DI Ports(Isolated), input Voltage: 5~24V DC; 4x DO Ports(Isolated), output Voltage: <60V DC	
SIM Card	1x Nano SIM Card Slot	


M.2 Slot	1x M.2 M-key 2280 Slot for NVMe SSD; 1x M.2 M-key 2280 Slot for AI Accelerator (pre-installed Hailo-8 M.2 AI Acceleration 26TOPS); 1x M.2 B-key 3042/3052 Slot for 5G/4G LTE	1x M.2 M-key 2280 Slot for NVMe SSD ; 1x M.2 M-key 2280 Slot for AI Accelerator; 1x M.2 B-key 3042/3052 Slot for 5G/4G LTE
Mini-PCle	1x Mini-PCle for LoRa module	
Control & Indication	4x LEDs; 1x Buzzer; 1x Reset Button	
HDMI	2 x HDMI 2.0	
Wireless Communication	Wi-Fi 2.4/5.0 GHz(On-chip); BLE 5.0(On-chip);	
	USB LoRa®*/SPI LoRa®*	
	4G LTE/5G*	
	USB Zigbee*	
Standards		
EMC	ESD: EN61000-4-2, Level 3; EFT: EN61000-4-4, Level 2; Surge: EN61000-4-5, Level 2	
Certification	CE, FCC, TELEC, RoHS, REACH	
Device Specification		
Ingress Protection	IP40	
Temperature	Operating Temperature -20~65°C Storage Temperature -40~85°C	
Operating Humidity	10~95% RH	
Reliability	SuperCAP UPS LTC3350 Module*	
	Hardware Watchdog: 1~255s	
	High Accuracy RTC	
Security	Encryption Chip TPM 2.0*	
	ATECC608A*	
Heat Dissipation	Fanless	
Warranty	2 years	
Production Lifetime	Until December 2036	
Dimension(W x H x D) & Weight(Net)	197.5 mm x 155 mm x 67.5 mm, 1280g	
Enclosure	6063 aluminum alloy heat sink, 5052 aluminum alloy enclosure	
Mounting	DIN-rail/Wall	
Statement	Options marked with * require additional purchase according to the bundle.	

Hardware Overview




- 1 2x RS485(Isolated) 4 x Isolated DI Ports
2x RS232(Isolated) 4 x Isolated DO Ports
2x CAN FD(Isolated)
- 2 2 x HDMI 2.0
- 3 3 x USB-A 3.0 Host 1 x USB-A 2.0 Host
- 4 Reset Hole
- 5 5 x Reserved Antenna Ports for Wireless
- 6 1 x 10/100/1000 Mbps(supports PoE PD)
1 x 10/100 Mbps IEEE 802.3/802.3u
- 7 Nano SIM Card Slot
- 8 USB-C 2.0 (For flashing OS & Debug)
- 9 Reboot Switch
- 10 4 x LED indicators
- 11 DC 9V~36V, 2-pin Terminal Block
- 12 Grounding point

Top View




- [03]UPS Module
- [02/06]Interface expansion board
- [01]Mini-PCIe Slot
- [09]PE Earth Block
- [01]Power In Terminal
- [020]485/232/DI&DO/CAN
- Boot Switch
- [132]USB-C 2.0 (flashing OS & Debug)
- [10]Nano SIM Card Slot
- [112/113]HDMI 2.0 x2
- [15]RJ45PoE/Ethernet(1000M)
- [14]RJ45Ethernet(100M)
- [16/113] 3 x USB-A 3.0; 1 x USB-A 2.0
- Reset Button
- RTC capacitor
- [029]M.2 B-Key Slot
- [024/025]PoE Module
- [07]M.2 M-Key NVMe SSD Slot

Bottom View



- [04/05]CMS Module
- [08]AI Accelerator(Optional)



Applications

- Manufacturing & Industrial Automation:** With rich industrial interfaces, the controller integrates seamlessly with different sensors, PLCs, and machinery, enabling efficient process monitoring and control. It supports multiple communication protocols for real-time data acquisition and remote equipment management, fostering a smarter and more efficient factory.
- AI-Powered Video Analytics & Surveillance:** Integrated into NVR systems for real-time video analytics, including anomaly detection, object detection, crowd monitoring and behavior analysis, enhancing situational awareness and security efficiency.
- Smart Transportation:** Acts as an AI/IoT gateway for real-time processing of visual data from multiple sensors and camera feeds at the edge, enabling intelligent traffic flow analysis and smart parking management to enhance transportation monitoring management capabilities.
- Smart Building:** Integrates sensors and IoT devices to monitor and optimize building systems such as lighting, HVAC, and security. Uses AI for energy efficiency, predictive maintenance, and occupant comfort, enhancing building management.
- Smart Retail:** Create innovative smart retail solutions using AI-driven features like real-time visual product recognition, personalized shopping experiences, and advanced customer behavior analytics for optimized store operations.

Part List

reComputer Industrial R2135-12	x 1
Mounting Bracket	x 2
Bracket Screw	x 4
DIN-rail Clip	x 1
DC Power Female Jack to Screw Terminal Adapter	x 1
12V/3A Power Adapter (with 4 interchangeable adapter plugs)	x 1
15*2-pin Terminal Block Connector (Male)	x 1
120Ω Resistor	x 5
Wi-Fi/BLE Antenna	x 1
User Manual	x 1

Compliance & Logistics

HSCODE	8471504090
USHSCODE	8517180050
UPC	
EUHSCODE	8471707000
COO	CHINA

Resource Links

- <https://www.seeedstudio.com/reComputer-Industrial-R2135-12-p-6547.html>
- [Seeed Raspberry Pi Flyer](#)
- [reComputer_Industrial_R2100_User_Mannual](#)
- [reComputer_Industrial_R2100_Schematic](#)
- [reComputer_Industrial_R2000/2100_3D_File](#)
- [Seeed Raspberry Pi Flyer-CN](#)
- [Seeed reComputer Industrial R Series Flyer](#)

Seeed Technology Co.,Ltd.
9F, Building G3, International E City,
Zhongshanyuan Road, Nanshan, Shenzhen, China

Tel: +86 0755-80695676
Web: www.seeed.cc
Shop: www.seeedstudio.com