

INDUSTRIAL PRODUCT DATASHEET

XIAO ePaper Display Board(ESP32-S3) - EE05

XIAO ePaper Display Board (ESP32-S3) - EE05: a versatile, no-code ePaper display solution powered by XIAO ESP32-S3 Plus for smart home dashboards, energy monitoring, security alerts, and digital photo frames.

SKU


100057220

UPDATED


2026-09-20 06:17:32

PRICE

\$9.90(Excl. VAT)



Overview







The XIAO ePaper Display Board (ESP32-S3) - EE05 is powered by XIAO ESP32-S3 Plus and supports a wide range of 24-pin ePaper displays. It features an extension IO port, a BAT connector with switch, and no-code UI design and deployment via SenseCraft HMI for applications such as smart home dashboards, energy monitoring, security alerts, and digital photo frames.

Key Features

- **Powered by XIAO ESP32-S3 Plus:** Works immediately when connected to a compatible ePaper display.
- **Versatile Display Support:** Compatible with a wide range of 24-pin ePaper displays, supporting 24-Pin epaper displays for various project requirements.
- **Extension IO Port:** Enables connection of additional sensors, such as temperature and humidity sensors, for enhanced functionality.
- **BAT Connector with Switch:** Provides simple battery connection and integrates a switch, enabling efficient power management and energy savings.
- **No-Code UI Design & Deployment with SenseCraft HMI:** Design and deploy personalized dashboards effortlessly with [SenseCraft HMI](#), our new AI-powered no-code platform. Create your UI through simple drag-and-drop elements, choose from our rich templates, or let AI help you. Connect real-time data from web APIs, then deploy your finished dashboard to epaper display with just a few clicks. From design to data configuration to deployment, everything happens seamlessly on one single platform.

Product Gallery






Specification

Parameter	Description
Processor	XIAO ESP32-S3 Plus
ePaper Connector	FPC 24 Pin 0.5mm
Battery Connector	JST 2.0mm
Switch	Battery Power ON/OFF
Power Supply	- 3.7V Li-Battery - USB Type-C
Button	-1x Reset button -3x User button
Software	Support SenseCraft HMI(SenseCraft HMI)
	Support Arduino/PlatformIO development platform

Hardware Overview



Applications

- **Smart Home Dashboard:** Display real-time information such as weather updates, calendar events, and notifications from various smart home devices.
- **Energy Monitoring:** Show energy consumption data from smart meters, helping homeowners track and manage their energy usage more efficiently.
- **Security Alerts:** Display alerts and notifications about security events, such as motion detection or door/window sensor activation.
- **Digital Photo Frame:** Create a WiFi-enabled digital photo frame that can display images from your smart home network.

Product								
Processor	XIAOESP32-S3 Plus	XIAOnRF52840 Plus	XIAOESP32-S3 Plus	XIAOnRF52840 Plus	XIAO ESP32-S3 Plus	XIAO ESP32-S3 Plus	N/A(Compatible with XIAO Series)	
Compatible Displays	24 Pin ePaper	24 Pin ePaper50 Pin ePaper			24 Pin ePaper			
Battery Connector	JST 2.0mm	JST 2.0mm	JST 2.0mm	JST 2.0mm	JST 2.0mm	/		
Battery Power ON/OFF	√	√	√	√	√	/		
Button	1x Reset,3x User	1x Reset,3x User	1x Reset3x User	1x Reset3x User	/			
Extension IO Port	√	/	/	/	√			
SenseCraft HMI	√	/	√	/	√	√	/	

Product	Name	Resolution	Display Color	Partial Refresh	SenseCraft HMI
		200x200		√	√
		250x122		√	√
		250x122			√
		212x104		√	
		296x128			
		296x128		√	√
		296x128			√
		400x300		√	
		800x480			√
		648x480		√	
		800x480			√
		800x480		√	√
		1404x1872		√	√
		1600x1200			√

Part List

XIAO ePaper Display Board EE05	×1
24Pin Adapter and 24Pin FFC Extension Cable	×1
2.4GHz FPC Antenna (2.9dBi)	×1

Compliance & Logistics

HSCODE	8543909000
USHSCODE	8543903500
UPC	
EUHSCODE	8471707000
COO	CHINA

Resource Links

- <https://www.seeedstudio.com/XIAO-ePaper-Display-Board-EE05-p-6755.html>
- [Wiki-XIAO ePaper Display Board EE05 Resources](#)

Seeed Technology Co.,Ltd.

9F, Building G3, International E City,
Zhongshanyuan Road, Nanshan, Shenzhen, China

Tel: +86 0755-80695676

Web: www.seeed.cc

Shop: www.seeedstudio.com