

INDUSTRIAL PRODUCT DATASHEET

reComputer Industrial R2036-10 - The Most Reliable and Powerful Raspberry Pi Edge AI/IOT Controller

reComputer Industrial R2036-10: the most reliable and powerful Raspberry Pi CM5 edge AI/IoT controller with -20°C to 65°C fanless industrial operation, isolated interfaces, optional 26 TOPS Hailo-8 AI, and wireless expansion for...

SKU

100083626

UPDATED


2026-09-20 06:36:28

PRICE

\$514.90(Excl. VAT)



Overview



The reComputer Industrial R2036-10 is a Raspberry Pi CM5-based edge AI/IoT controller built around the Broadcom BCM2712 quad-core Arm Cortex-A76 64-bit SoC @ 2.4GHz, with up to 16GB RAM and 64GB eMMC, fanless cooling for -20°C to 65°C operation, and industrial-grade features including high-accuracy RTC, hardware watchdog, optional UPS supercapacitor and TPM/ATECC608A, IP40 aluminum enclosure, and DIN-rail/wall mounting. It provides rich isolated connectivity (3x RS485, 1x RS232, 8x DI, 8x DO, Gigabit Ethernet with PoE, 2x HDMI 2.0, multiple USB ports, Nano SIM) and supports optional Hailo-8 AI acceleration up to 26 TOPS plus wireless expansion via Mini-PCIe for LTE/LoRa®/Zigbee and M.2 B-Key for 4G/5G.

Key Features

Note: Options marked with require additional purchase according to the **bundle**.


- For 4G functionality, both a 4G module and a 4G antenna must be selected.
- For GPS functionality, both a 4G module and a GPS antenna must be selected.
- For LoRaWAN® functionality, LoRaWAN® module must be selected.
- **Price Increase Announcement**


Date: March 2, 2026

Due to increased demand for modules and SSDs, reComputer' pricing is expected to rise by approximately \$20–\$80 in the coming weeks. Please confirm your orders and requirements accordingly to help secure availability.

- **Powerful Performance with Raspberry Pi CM5:** Broadcom BCM2712 quad-core Arm Cortex-A76 64-bit SoC @ 2.4GHz. Features up to 16GB RAM and 64GB eMMC.
- **Robust Heat Dissipation:** High-performance fanless cooling, engineered to handle the intense heat of AI workloads and ensure stable operation from -20°C to 65°C.
- **Industrial-Grade Reliability:** High Accuracy RTC, hardware watchdog and optional UPS supercapacitor. Optional TPM/ATECC608A. IP40, aluminum alloy enclosure provides industrial-grade protection. Supports DIN-rail and wall mounting. Guaranteed production until at least December 2036.
- **AI-Optimized Computing:** With the optional Hailo-8 AI accelerator, it delivers up to 26 TOPS, enabling real-time, high-performance AI vision processing across multiple channels.
- **Rich Industrial Connectivity:** 3x RS485, 1x RS232, 8x DI, 8x DO, all isolated. 1x 10M/100M/1000M Ethernet (PoE), 1x 10M/100M Ethernet. 2x HDMI 2.0. 3x Type-A USB3.0, 1x Type-A USB2.0, 1x Type-C USB2.0 (for OS update). 1x Nano SIM card slot.
- **Versatile Wireless Connectivity:** On chip Wi-Fi and BLE. Flexible expansion via Mini-PCIe for LTE, LoRa®, Zigbee. M.2 B-Key for 4G/5G.

Product Gallery








Specification

Hardware Specification		
Product Series	R20xx-12	R20xx-10
CPU	Raspberry Pi Compute Module 5, 2.4GHz quad-core 64-bit Arm Cortex-A76	
AI Processor	1x Pre-installed Hailo-8 M.2 AI Acceleration, 26TOPS	*
Operating System	Raspbian, Debian	
Memory & Storage	2GB/4GB/8GB/16GB RAM, 16GB/32GB/64GB eMMC	
System Specification		
Power Input	DC 9V~36V, 2-pin Terminal Block	
PoE(as powered device)	IEEE 802.3 at Standard 25.5W PoE	
Power Switch	No	
Reboot Switch	Yes	
Interface		
Ethernet & USB	1x 10/100/1000 Mbps(supports PoE PD); 1x 10/100 Mbps IEEE 802.3/802.3u	
	3x USB-A 3.0 Host; 1x USB-A 2.0 Host; 1x USB-C 2.0 (For flashing OS & Debug)	
COM and I/O	3x RS485(Isolated); 1x RS232(Isolated)	
	8x DI Ports(Isolated), input Voltage: 5~24V DC; 8x DO Ports(Isolated), output Voltage: <60V DC	

SIM Card	1x Nano SIM Card Slot	
M.2 Slot	1x M.2 M-key 2280 Slot for NVMe SSD; 1x M.2 M-key 2280 Slot for AI Accelerator (pre-installed Hailo-8 M.2 AI Acceleration 26TOPS); 1x M.2 B-key 3042/3052 Slot for 5G/4G LTE	1x M.2 M-key 2280 Slot for NVMe SSD ; 1x M.2 M-key 2280 Slot for AI Accelerator; 1x M.2 B-key 3042/3052 Slot for 5G/4G LTE
Mini-PCle	1x Mini-PCle for LoRa module	
Control & Indication	4x LEDs; 1x Buzzer; 1x Reset Button	
HDMI	2 x HDMI 2.0	
Wireless Communication	Wi-Fi 2.4/5.0 GHz(On-chip); BLE 5.0(On-chip);	
	USB LoRa®*/SPI LoRa®*	
	4G LTE/5G*	
	USB Zigbee*	
Standards		
EMC	ESD: EN61000-4-2, Level 3; EFT: EN61000-4-4, Level 2; Surge: EN61000-4-5, Level 2	
Certification	CE, FCC, TELEC, RoHS, REACH	
Device Specification		
Ingress Protection	IP40	
Temperature	Operating Temperature -20~65°C Storage Temperature -40~85°C	
Operating Humidity	10~95% RH	
Reliability	SuperCAP UPS LTC3350 Module*	
	Hardware Watchdog: 1~255s	
	High Accuracy RTC	
Security	Encryption Chip TPM 2.0*	
	ATECC608A*	
Heat Dissipation	Fanless	
Warranty	2 years	
Production Lifetime	Until December 2036	
Dimension(W x H x D) & Weight(Net)	197.5 mm x 155 mm x 67.5 mm, 1280g	
Enclosure	6063 aluminum alloy heat sink, 5052 aluminum alloy enclosure	
Mounting	DIN-rail/Wall	
Statement	Options marked with * require additional purchase according to the bundle .	

Hardware Overview





Applications

- **Manufacturing & Industrial Automation:** With rich industrial interfaces, the controller integrates seamlessly with different sensors, PLCs, and machinery, enabling efficient process monitoring and control. It supports multiple communication protocols for real-time data acquisition and remote equipment management, fostering a smarter and more efficient factory.
- **AI-Powered Video Analytics & Surveillance:** Integrated into NVR systems for real-time video analytics, including anomaly detection, object detection, crowd monitoring and behavior analysis, enhancing situational awareness and security efficiency.
- **Smart Transportation:** Acts as an AI/IoT gateway for real-time processing of visual data from multiple sensors and camera feeds at the edge, enabling intelligent traffic flow analysis and smart parking management to enhance transportation monitoring management capabilities.
- **Smart Building:** Integrates sensors and IoT devices to monitor and optimize building systems such as lighting, HVAC, and security. Uses AI for energy efficiency, predictive maintenance, and occupant comfort, enhancing building management.
- **Smart Retail:** Create innovative smart retail solutions using AI-driven features like real-time visual product recognition, personalized shopping experiences, and advanced customer behavior analytics for optimized store operations.

Part List

reComputer Industrial R2036-10	x 1
Mounting Bracket	x 2
Bracket Screw	x 4
DIN-rail Clip	x 1
DC Power Female Jack to Screw Terminal Adapter	x 1
12V/3A Power Adapter (with 4 interchangeable adapter plugs)	x 1
15*2-pin Terminal Block Connector (Male)	x 1
120Ω Resistor	x 5
Wi-Fi/BLE Antenna	x 1
User Manual	x 1

Compliance & Logistics

HSCODE	8471504090
USHSCODE	8517180050
UPC	
EUHSCODE	8471707000
COO	

Resource Links

- <https://www.seeedstudio.com/reComputer-Industrial-R2036-10-p-6966.html>
- [Seeed Raspberry Pi Flyer](#)
- [reComputer_Industrial_R2000_User_Mannual](#)
- [reComputer_industrial_R2000_Schematic](#)
- [reComputer_Industrial_R2000/2100_3D_File](#)
- [Seeed Raspberry Pi Flyer-CN](#)
- [Seeed reComputer Industrial R Series Flyer](#)

Seeed Technology Co.,Ltd.
9F, Building G3, International E City,
Zhongshanyuan Road, Nanshan, Shenzhen, China

Tel: +86 0755-80695676
Web: www.seeed.cc
Shop: www.seeedstudio.com