seeed studio

INDUSTRIAL PRODUCT DATASHEET

Industrial Soil Moisture & Temperature Sensor MODBUS-RTU RS485, 0-2V Analog Voltage (S-Soil MT-02A)

An IP68 RS485 Soil Moisture and Temperature Sensor ranges - from 0% to 100% of saturation and -40℃ ~ +80℃.

SKU	UPDATED	PRICE
101990668	2026-11-11 10:10:58	$79.00(Excl. VAT)



Overview



An IP68 RS485 Soil Moisture and Temperature Sensor ranges - from 0% to 100% of saturation and -40℃ ~ +80℃. Used in soil applications like water-saving irrigation and greenhouse management. Use the sensor with SenseCAP Data Logger for seamless data collection and management.

Key Features

01 **High Performance**

high accuracy, reliability, and stability

02 **Universal Protocol**

MODBUS-RTU RS485 and 0~2V Analog Voltage

03 **Wide-range Power Supply**

Can be powered with supply voltage within 3.6V ~ 30V and 3.9V ~ 30V


04 **Strong Robustness**

anti-corrosion, with excellent performance for long-term use

05 **Safety**

designed with reverse voltage protection

Product Gallery







Applications

- **Water-saving irrigation,Scientific Experiments,Greenhouse Management,Horticulture and Gardening,Golf turf Management,Smart Agriculture,Other Environmental Monitoring Scenarios**

Resource Links

- https://www.seeedstudio.com/RS485-Soil-Moisture-Temperature-Sensor-S-Soil-MT-02-p-4634.html
- Datasheet for Soil Moisture & Temperature Sensor MODBUS-RTU RS485 (S-Soil MT-02A)
- User Manual (V1.0) for Soil Moisture & Temperature Sensor MODBUS-RTU RS485 (S-Soil MT-02A)
- User Manual (V2.0) for Soil Moisture Temperature Sensor MODBUS-RTU RS485 & 0-2V Analog Voltage

Seeed Technology Co.,Ltd.
9F, Building G3, International E City,
Zhongshanyuan Road, Nanshan, Shenzhen, China

Tel: +86 0755-80695676
Web: www.seeed.cc
Shop: www.seeedstudio.com