
seeed studio

INDUSTRIAL PRODUCT DATASHEET


Raspberry Pi Compute Module 4 - 8GB RAM, 32GB eMMC, 2.4/5.0GHz Wi-Fi & Bluetooth 5.0 (CM4108032)

This version of the Raspberry Pi Compute Module 4 includes a high-performance 64-bit quad-core processor, 8GB LPDDR4 RAM, 32GB eMMC, dual-display support at resolutions up to 4K, hardware video decode at up to 4Kp60, Gigabit...

SKU	UPDATED	PRICE
102991441	2026-11-11 08:37:22	$195.00(Excl. VAT)



Overview



This version of the Raspberry Pi Compute Module 4 includes a high-performance 64-bit quad-core processor, 8GB LPDDR4 RAM, 32GB eMMC, dual-display support at resolutions up to 4K, hardware video decode at up to 4Kp60, Gigabit Ethernet, USB 2.0, dual camera interfaces, PCIe Gen 2 x1 interface, and dual-band 2.4/5.0GHz wireless LAN and Bluetooth 5.0. Recommended Upgrade RK3576 Module 8GB RAM/64GB 8GB module matched with 8GB+64GB. Better for production carriers. View RK Alternative →

Key Features

01 High-performance 64-bit Quad-core Cortex A72 processor

02 More memory options (1GB/2GB/4GB/8GB), suitable for large data compilation

03 Dual display（HDMI) support at resolutions up to 4K

04 Faster eMMC flash with up to 100 MB/s transfer rate, 4x faster than CM3+


05 Added wireless module option with on-board PCB antenna and external antenna for industrial applications


06 Designed with B to B connectors for enhanced stability


07 Add on-board Gigabit Ethernet design, support IEEE1588, suitable for network application development

08 Add PCIe interface expansion, can flexibly add related modules

Product Gallery







Resource Links

- https://www.seeedstudio.com/Raspberry-Pi-Compute-Module-CM4108032-p-5220.html
- Raspberry Pi Compute Module 4 product brief
- Raspberry Pi Compute Module 4 datasheet
- Compute Module 4 STEP file

Seeed Technology Co.,Ltd.
9F, Building G3, International E City,
Zhongshanyuan Road, Nanshan, Shenzhen, China

Tel: +86 0755-80695676
Web: www.seeed.cc
Shop: www.seeedstudio.com