seeed studio

INDUSTRIAL PRODUCT DATASHEET

Battery Detector with Polymer Lithium Ion 1050mAh 3.7V

Battery Detector with Polymer Lithium Ion 1050mAh 3.7V: a 3.7V 1050mAh LiPo battery and 4-LED battery indicator supporting JST-1.0/JST-2.0 connectors for portable projects.

SKU	UPDATED	PRICE
110060468	2026-10-23 03:06:45	$8.95(Excl. VAT)



Overview



This battery kit includes a 3.7V 1050mAh polymer lithium-ion battery and a battery indicator for testing remaining charge in portable 3.7V projects. The indicator supports JST-1.0 and JST-2.0 connectors with a solderable pad for 2.54 pin headers, uses 4 LEDs for 25% charge levels and an ERROR LED for wrong connection, and tests one battery at a time up to 9V.

Key Features

Description

“I really should test my battery when I am out.” If you ever said that to yourself when you find out you just packed up a dead battery for your portable project, you really should get one of this battery kit.

The kit comes in two parts, a **3.7V 1050mAh Lipo battery** and a **battery indicator**. The battery has a maximum discharging current of 1050mA and can work as the power supply for any of your portable projects that running at 3.7V.

As for the good mate of your batteries, the battery indicator comes very handy when you need to test how much power you have left. There are 2 different standard battery connectors available on board, JST-1.0 and JST-2.0, which covers the most commonly used battery connectors in the market. We also left you a soldering pad for 2.54 pin headers in case your battery does not fit any of it. You can only test ONE BATTERY AT A TIMEand the battery voltage should be NO HIGHER THAN 9V. The current battery level of your battery is described with 4 LEDs, each one represents a battery level of 25%. An ‘ERROR’ LED indicator is also used to detect if you’ve connected the battery in a wrong way.

Note: Test your batteries one at a time, and do not connect battery higher than 9V!

Features

- 3.7V 1050mAh Lipo Battery for portable projects
- Easy-to-use battery indicator with different standard of battery connectors

Specification

The Batter Indicator:

- Detect Range: 3-4.2V
- Working current: 15 mA
- 4 LED indicators for battery level
- 1 ‘Error’ LED indicator for wrong connection
- Supports JST-1.0 and JST-2.0 battery connector
- Solderable pad for 2.54 pin headers
- Dimension: 30mm x 25mm

Battery:

- Operating Temperature: 0 ~45°C (Charging) / -10~60°C (Discharging)
- Capacity: 1050mAh
- Nominal voltage: 3.7 V
- Connector：JST- 2.0
- Maximum Discharge current: 1050mA
- Maximum Charge Current: 1050mA
- Dimension: 45mm x 48mm x 4.9mm

Part List

- 1x Battery Indicator

- 1x 1050mAh 3.7V Lipo Battery

Documents

- For libraries and documents, please visit our **Wiki** page.
- For technical discussion, please come to our **Forum**.
- For projects that you would like to share with the community, please visit **Recipe**.

Product Gallery











Part List

- Operating Temperature: 0 ~45°C (Charging) / -10~60°C (Discharging)
- Capacity: 1050mAh
- Nominal voltage: 3.7 V
- Connector：JST- 2.0
- Maximum Discharge current: 1050mA
- Maximum Charge Current: 1050mA
- Dimension: 45mm x 48mm x 4.9mm

- 1x Battery Indicator
- 1x 1050mAh 3.7V Lipo Battery

Compliance & Logistics

HSCODE	8503001000

Resource Links

- https://www.seeedstudio.com/Battery-Detector-with-Polymer-Lithium-Ion-1050mAh-3-7V-p-2648.html
- Schematic(Eagle) file
- CN1185 Datasheet
- Battery Usage Datasheet
- Battery Safety Datasheet and Certificates

Seeed Technology Co.,Ltd.
9F, Building G3, International E City,
Zhongshanyuan Road, Nanshan, Shenzhen, China

Tel: +86 0755-80695676
Web: www.seeed.cc
Shop: www.seeedstudio.com