
seeed studio

INDUSTRIAL PRODUCT DATASHEET

Grove - LoRa Radio 433MHz

Using RFM95 module based on SX1276 LoRa® Inputting voltage：5V/3.3V ~28mA(Avg) @+20dBm continuous transmit ~8.4mA(Avg)@standby mode ~20mA(Avg) @receive mode, BW-500kHz

SKU	UPDATED	PRICE
113060007	2026-11-11 07:55:25	$13.87(Excl. VAT)




Overview





Using RFM95 module based on SX1276 LoRa® Inputting voltage：5V/3.3V ~28mA(Avg) @+20dBm continuous transmit ~8.4mA(Avg)@standby mode ~20mA(Avg) @receive mode, BW-500kHz


Product Gallery











Resource Links

- https://www.seeedstudio.com/Grove-LoRa-Radio-433MHz-p-2777.html

Seeed Technology Co.,Ltd.
9F, Building G3, International E City,
Zhongshanyuan Road, Nanshan, Shenzhen, China

Tel: +86 0755-80695676
Web: www.seeed.cc
Shop: www.seeedstudio.com