seeed studio

INDUSTRIAL PRODUCT DATASHEET

SenseCAP Indicator D1 - 4-inch ESP32-S3 Touchscreen for AI Desk Gadgets

SenseCAP Indicator D1 is a 4-inch ESP32-S3 and RP2040 dual-MCU touchscreen for AI desk gadgets and open-source IoT development with Wi-Fi/BLE/LoRa® connectivity.

SKU	UPDATED	PRICE
114993068	2026-10-23 02:44:20	$49.00(Excl. VAT)



Overview



SenseCAP Indicator D1 is a 4-inch touchscreen development platform driven by ESP32-S3 and RP2040 dual-MCU, supporting Wi-Fi/BLE/LoRa® communication, Type-C and Grove interfaces, and rich GPIOs for IoT projects. It can serve as a desktop air quality detector, LoRa® Hub with Matter over Wi-Fi, weather station display, sensor data dashboard, smart home assistant, or third-party platform integration with AWS, ChatGPT, Matter, NodeRED, and IoTex.

Key Features

Note

SenseCAP Indicator has FCC, CE, RoHS, and REACH certifications for all models (D1, D1S, D1L, D1Pro), and TELEC certification formal certificate for D1, D1S versions. Please download the certificate **here**.

For big quantity orders please contact **iot@seeed.cc**.

SenseCAP Indicator is a 4-inch touch screen driven by ESP32 and RP2040 dual-MCU and supports Wi-Fi/BLE/LoRa® communication.

The board comes with Type-C and Grove interfaces, supports ADC and IIC transmission protocols, and can easily connect to other peripherals with rich GPIOs.

SenseCAP Indicator is a fully open-source powerful IoT development platform for developers. One-stop ODM Fusion service is also available for customization and quick scale-up.

- **A screen for your AI workflow:** Build coding-agent status displays, Muse image screens and custom desk interfaces using open-source projects.
- **4-inch capacitive touchscreen:** A 480 × 480 display for status cards, project information and custom touch controls.
- **ESP32-S3 + RP2040:** A dual-MCU platform with Wi-Fi/BLE and Grove expansion for your own projects.
- **Enclosed and USB-powered:** Start with a desktop device with its housing already in place.
- **Choose your software:** Explore SDK examples, ESPHome/LVGL configurations and community projects, then configure the firmware for your use case.


Product Gallery











Specification

Screen	3.95 Inch, Capacitive RGB Touch Screen
Screen Resolution	480 x 480 pixels
Power Supply	5V DC, 1A

Battery	N/A
Processor	ESP32-S3: Xtensa® dual-core 32-bit LX7 microprocessor, up to 240MHz RP2040: Dual ARM Cortex-M0+ up to 133MHz
Flash	ESP32S3: 8MB RP2040: 2MB
External Storage	Support up to 32GB Micro SD Card (not included)
Wi-Fi	802.11b/g/n, 2.4GHz
Bluetooth	Bluetooth 5.0 LE
Buzzer	MLT-8530, Resonant Frequency：2700H

Hardware Overview

Model	D1	D1S	D1L	D1Pro
tVOC sensor	/	◉	/	◉
CO2 sensor	/	◉	/	◉
Grove TH Sensor	/	◉	/	◉
LoRa (SX1262)	/	/	◉	◉
Wi-Fi	◉	◉	◉	◉
Bluetooth	◉	◉	◉	◉

Applications

- **Desktop Air Quality Detector:** SenseCAP Indicator native firmware enables you to use it as a desktop air quality detector or you could customize one of your own styles. There are built-in tVOCs and CO2 sensors, and a Grove TH sensor is provided to connect externally to reduce heat interference to get more accurate temperature and humidity results.
- **LoRa® Hub with Matter over Wi-Fi:** The embedded SX1262 LoRa® module enables you to build the LoRa® application and connect your local LoRa® sensors to the Cloud via Wi-Fi. For example, you could build a LoRa® hub device to connect your LoRa® sensors to your smart home ecosystem to implement Matter over Wi-Fi. In this way, the LoRa® devices could be connected to the Matter ecosystem via Wi-Fi, without the need to buy a new Matter-compatible device.
- **Air Quality Monitor**
- **Weather Station Display**
- **Sensor Data Dashboard**
- **Smart Home Assistant**
- **Mini Sensor Hub**
- **Stock Price Indicator**
- **Digital Album**
- **Standard Operation Procedure Reminder**
- **Third-party Platform Integrations:** It can also be used to develop various exciting applications integrating with third-party platforms, such as AWS / ChatGPT / Matter / NodeRED / IoTex ...

Part List

SenseCAP Indicator	x1
USB Type-C Cable (1m)	x1
Grove AHT20 TH Sensor (For D1S and D1Pro version)	x1

Compliance & Logistics



HSCODE	8517180050
USHSCODE	8531200020
UPC	
EUHSCODE	8543709099
COO	CHINA

FCC Requirement

Any changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions:

(1) this device may not cause harmful interference, and

(2) this device must accept any interference received, including interference that may cause undesired operation.

15.21

This transmitter must not be co-located or operating in conjunction with any other antenna or transmitter.

Note: This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to Part 15 of the FCC Rules.

These limits are designed to provide reasonable protection against harmful interference in a residential installation.

This equipment generates, uses, and can radiate radio frequency energy.

If not installed and used in accordance with the instructions, it may cause harmful interference to radio communications.

However, there is no guarantee that interference will not occur in a particular installation.

If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

Resource Links

- https://www.seeedstudio.com/SenseCAP-Indicator-D1-p-5643.html
- User Guide for RS485 & 0-2V pH Sensor (S-pH-01) - v2.0.pdf
- User Manual for the Industrial pH Meter/ Sensor Modbus-RTU RS485 & 4~20mA Current (S-pH-01A)
- Datasheet for the Industrial pH Meter/ Sensor Modbus-RTU RS485 & 4~20mA Current (S-pH-01A)
- pH Sensor Calibration

Seeed Technology Co.,Ltd.
9F, Building G3, International E City,
Zhongshanyuan Road, Nanshan, Shenzhen, China

Tel: +86 0755-80695676
Web: www.seeed.cc
Shop: www.seeedstudio.com