
seeed studio

INDUSTRIAL PRODUCT DATASHEET


reComputer Jetson AGX Orin™ Developer Kit Bundle

Compact embedded AI developer kit with up to 275 TOPS and extensive I/O for advanced robotics and edge AI applications.

SKU	UPDATED
E26021201	2026-03-16 03:39:46



Overview



The reComputer Jetson AGX Orin™ Developer Kit Bundle is a powerful embedded AI platform with the Jetson AGX Orin module delivering up to 275 TOPS and a choice of 32GB or 64GB 256-bit LPDDR5 memory. It features rich I/O including 2x CAN, 4x USB, 2x Ethernet, RS-485, I2S, DI/DO, HDMI 2.1, and a 128GB NVMe SSD in a compact 110mm x 110mm form factor, suitable for humanoid robotics, autonomous navigation, generative edge AI, and computer vision applications.

Key Features

The reComputer Jetson AGX Orin™ Developer Kit Bundle is an excellent development platform providing extensive I/O connectivity and high-speed memory for AI projects. This bundle features a carrier board equipped with 2x CAN, 4x USB, 2x Ethernet, 1x RS-485, 1x I2S, 4x DI/DO (DO configurable as UART), and 1x HDMI 2.1, alongside a 128GB NVMe M.2 PCIe SSD. To support high-performance computing, it comes with choice of 32GB or 64GB 256-bit LPDDR5 memory to easily handle demanding workloads. Ideal for applications such as humanoid robotics, multi-Sensor fusion for autonomous mapping & navigation, generative edge AI, and computer vision.


- **Powerful embodied AI Platform** Compatible with the Jetson AGX Orin module, offering up to 275 TOPS. Perfect platform for embodied AI developm
- **Ultra Compact Size** 110mm x 110mm footprint, suitable for robot prototyping and development, especially robots that has tight footprint such as humanoids
- **Wide Voltage Input Range** Can be used in 48V battery power system (max 54V input)
- **Rich IO capabilities** Includes most common IOs used in robotics prototyping, such as USB, 10G Ethernet, CAN, RS-485 and I2S

Product Gallery


















Specification


Product	reComputer Mini J501 Carrier Board	
Storage	1x M.2 Key M slot	
Networking	1x M.2 Key E slot for WiFi/Bluetooth module	
I/O	USB	2x USB 3.2 Type-A (10Gbps); 1x USB 3.0 Type-C (Recovery); 1x USB 2.0 Type-C (Debug);
	RJ45	1x 1G Ethernet 1x 10G Ethernet
	CAN	2x CAN （CAN-FD supported)
	RS485	1x RS-485
	I2S	1x I2S
	DI/DO	4x DI 4x DO (DO can be configured as UART)
	Display	1x HDMI 2.1
	Fan	1x 4 pin Fan Connector (12V PWM)
	Button	1x Reset Button; 1x Recovery Button
	RTC	1x RTC 2-pin
Power	1 x XT30 Connector (19-48V DC)	
Mechanical	Dimensions (W x D x H)	110mm x 110mm x 38mm
	Weight	90g
	Installation	Desk, wall-mounting
Operating Temperature	-10℃~60℃ （with thermal grease) -10℃~55℃ （with thermal pad)	
Warranty	2 Year	

Hardware Overview


Carrier Board - Bottom View



Carrier Board - Side View



Carrier Board - Top View



Applications

- **Humanoid Robotics**
- **AIRobotDevelopment:** With AGX Orin module, this most powerful embedded AI system lets you create advanced robotics and edge AI applications for manufacturing, logistics, and healthcare. It's the most powerful embedded system, pushing the limits of AI robotics. The Isaac robotics platform offers NVIDIA-accelerated systems, libraries, and generative AI models to enhance AI perception, manipulation, and simulation in robotics. LearnaboutIssacplatform Isaac - AI Robot Development Platform | NVIDIA Developer
- **Multi-Sensor Fusion for Autonomous Mapping & Navigation:** reComputer Mini J501 supports sensor-rich autonomy by integrating data from LiDAR (via Ethernet/CAN), 3D cameras (via USB/CSI), GPS, and IMU (via UART). Using AI models and algorithms like ORB-SLAM,A-LOAM, or Nav2, it performs sensor fusion, real-time localization, path planning, and obstacle avoidance. The low-latency processing on the Orin NX SoC allows autonomous systems to adapt to changing terrain or obstacles on the fly. Its wide voltage input and compact form factor make it suitable for mobile deployment, enabling robust, edge-level autonomy without external compute. Learn more about sensor options compatible with reComputer Mini J501 to get started.
- **Capable of Bringing Generative AI to the Edge:** Now you can build AI agents capable of processing large amounts of live or archived videos and images withVision-Language Models (VLM) such as LLaVA,this new AI agents help nearly every industry summarize, search, and extract actionable insights from video using natural language.
- **Fastest Way to Deploy Generative AI and Computer Vision Models:** We have jetson-exampleprepared for you! It offersone-line deploy projects edge AI applications of generative AI including Ollama, Llama3; computer vision including YOLOv8; and others. We have configured all environment for you to provides single command deployment of projects.

Part List

Seeed Carrier Board (reComputer Mini J501)	x1
Power Board	x1
XT30 to DC power cable	x1
USB Type-C to Type-A cable	x1
GH-1.25 4-pin 100mm JST Cable	x3
GH-1.25 6-pin 100mm JST Cable	x3
M2.5*4 Screw	x1
M2*6 Screw	x3
M2.5*25 Stud	x4
M2.5*8 Screw	x4

Resource Links

- https://www.seeedstudio.com/reComputer-Jetson-AGX-Orintm-Developer-Kit-Bundle.html
- Datasheet
- CarrierBoardSchematic
- PowerBoardSchematic
- 3D File
- Seeed Nvidia Jetson Product Catalog
- Nvidia Jetson Comparison
- Nvidia Jetson Product Comparison
- Seeed Nvidia Jetson Success Cases
- Seeed Jetson One Pager

Seeed Technology Co.,Ltd.
9F, Building G3, International E City,
Zhongshanyuan Road, Nanshan, Shenzhen, China

Tel: +86 0755-80695676
Web: www.seeed.cc
Shop: www.seeedstudio.com