TEST REPORT

REPORT No.: DTI2026OT010820A Date:2026-09-09

Applicant Company Name:Nabu Casa, Inc.

Applicant Company Address:1500 Valley House Drive Suite 210, Rohnert Park, CA 94928, United States

Report on the submitted samples said to be:

Sample Name	:	Home Assistant Connect AUX-2
Model No.	:	NC-AUX-9758
Manufacturer	:	Nabu Casa, Inc.
Manufacturer Address	:	1500 Valley House Drive Suite 210, Rohnert Park, CA 94928, United States
Sample Receiving Date	:	August 20, 2026;September 07, 2026
Testing Period	:	From August 20, 2026 to August 25, 2026; From September 07, 2026 to September 09, 2026
Results	:	Please refer to next page(s).

****

Summary of Test Results:

	TEST REQUEST	CONCLUSION
A	(EU) 2025/40 Packaging and Packaging Waste Regulation(PPWR) Article 5(4) on Total Lead, Cadmium, Mercury and Hexavalent Chromium content.	**Pass**

****

Shenzhen Deesev Testing International Corporation

Approved by: _____
Tommy Jiang / Lab Manager

Any holder of this document is advised that information contained hereon reflects the company's findings at the time of its intervention only and within the limits of client's instructions,if any.The company's sole responsibility is to its client and this document does not exonerate parties to atransaction from exercising all their rights and obligations under the transaction documents.This document cannot be reproduced execept in full,without prior written approval of the company.Any unauthorized alteration,forgery of falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.

Results:

Tested part(s):

1 Label

2 Paper box with multicolor ink

A、(EU) 2025/40 Packaging and Packaging Waste Regulation(PPWR) Article 5(4) on Total Lead, Cadmium, Mercury and Hexavalent Chromium content

Test method:

Lead, Cadmium, Mercury Content：
With reference to IEC 62321-4:2013+AMD1:2017CSV and IEC62321-5:2013, by acid digestion and analysis was performed by Inductively Coupled Plasma- Optical Emission Spectrophotometer (ICP-OES)

Hexavalent Chromium Content:
With reference to IEC 62321-7-2:2017 and IEC 62321-7-1:2015, by alkaline digestion and analysis was performed by UV-visible spectrophotometer (UV-Vis)

Item	Unit	MDL	Results	Limit
			1+2	
Lead (Pb)	mg/kg	2	ND	/
Cadmium (Cd)	mg/kg	2	ND	/
Mercury (Hg)	mg/kg	2	ND	/
Hexavalent Chromium (Cr^{6+})	mg/kg	8	ND	/
Total (Pb+Cd+Hg+Cr^{6+})	mg/kg	/	ND	⩽100
Conclusion	/	/	**Pass**	/

Remark:


- MDL = Method Detection Limit
- mg/kg =ppm
- ND = Not detected
- Decision rule: According to DTI-CX-39:Decision rule for conformity of the test results.
- Flow chart appendix is included.
- Photo appendix is included.

****


Any holder of this document is advised that information contained hereon reflects the company's findings at the time of its intervention only and within the limits of client's instructions,if any.The company's sole responsibility is to its client and this document does not exonerate parties to atransaction from exercising all their rights and obligations under the transaction documents.This document cannot be reproduced except in full,without prior written approval of the company.Any unauthorized alteration,forgery of falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.

Appendix

Test flow chart for Lead ,Mercury& Cadmium Content:




Test Flowchart for Cr^{6+} content



****

Any holder of this document is advised that information contained hereon reflects the company's findings at the time of its intervention only and within the limits of client's instructions,if any.The company's sole responsibility is to its client and this document does not exonerate parties to atransaction from exercising all their rights and obligations under the transaction documents.This document cannot be reproduced execept in full,without prior written approval of the company.Any unauthorized alteration,forgery of falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.

Photograph of Sample



Any holder of this document is advised that information contained hereon reflects the company's findings at the time of its intervention only and within the limits of client's instructions,if any.The company's sole responsibility is to its client and this document does not exonerate parties to atransaction from exercising all their rights and obligations under the transaction documents.This document cannot be reproduced execept in full,without prior written approval of the company.Any unauthorized alteration,forgery of falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.



*** End of Report ***

Any holder of this document is advised that information contained hereon reflects the company's findings at the time of its intervention only and within the limits of client's instructions,if any.The company's sole responsibility is to its client and this document does not exonerate parties to atransaction from exercising all their rights and obligations under the transaction documents.This document cannot be reproduced execept in full,without prior written approval of the company.Any unauthorized alteration,forgery of falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.