JAPAN MIC
TYPE CERTIFICATION
CERTIFICATE NUMBER 217-263366

CERTIFICATE HOLDER:

Company Name	:	Seeed Technology Co., Ltd.
Postal Address	:	9F, Building G3, TCL International E city, Shuguang Community, Xili street, Nanshan, Shenzhen, Guangdong Province, P.R.C
Representative Name	:	Albert Miao, albert.miao@seeed.cc

MANUFACTURER:

Company Name	:	Seeed Technology Co., Ltd.
Postal Address	:	9F, Building G3, TCL International E city, Shuguang Community, Xili street, Nanshan, Shenzhen, Guangdong Province, P.R.C

PRODUCT DESCRIPTION

Product Name	:	Seeed Studio Wio-LR2021 Wireless module
Trademark/Trade Name	:	Seeed Studio
Model Number(s)	:	Seeed Studio Wio-LR2021 Wireless module
Category	:	Unlicensed Device (Act 38-2-2.1.1)

Based on the evidence presented in the Technical Documentation, IIA Lab Services, LLC, as a Registered Certification and Approval Body (217) recognized by Japan MIC, declares that the listed product is in conformity with the Technical Regulations Conformity Certification of Specified Radio Equipment, and the Technical Specifications.

The products placed on the Japanese market must bear the following marking:

R 217-263366

This certificate is limited to products that are identical to the type assessed for this application for certification and is issued under the provision that IIA Lab Services, LLC nor its subsidiary companies accept any liability concerning the contents of this document other than forced by law. Reproduction of the Certificate (with Annex) in full is allowed. Reproduction of parts of this certificate may only be allowed by written permission of IIA Lab Services, LLC.

RECOGNIZED CERTIFICATION BODY
Certificate issued by: IIA Lab Services, LLC (217)
Name and Signature: Bruno Clavier
Date: September 29, 2026

PRODUCT SPECIFICATIONS

Low power data communications system in the 2.4GHz band
Item19,Paragraph1,Article2

F1D 2402-2480MHz(1000kHz Sep 79ch)	5.8000mW
F1D 2403-2479MHz(1000kHz Sep 77ch)	5.8000mW

Specified Low Power Radio Equipment / Tele-control, Tele-meter and Data Transmission
Item8,Paragraph1,Article2

X1D 920.6-928.0MHz(200KHz Sep 38ch)	1.65mW
X1D 920.7-927.9MHz(200kHz Sep 37ch)	11.00mW

Antenna

Model	Antenna Type	Antenna Gain
V1194-145-A-01	Lora-Fiberglass Omni-directional Antenna	5.85 dBi
M01-0401030R0A	Lora-FPC Antenna	1.11 dBi
M02-0200290R0A	2.4G-Dipole Antenna	2.35 dBi
M01-0601930R0A	2.4G-FPC Antenna	2.53 dBi
M04-0105060R0A	2.4G-Helical Antenna	2.55 dBi
M02-0600110R0A	2.4G-Fiberglass Omni-directional Antenna	5.03 dBi