

SenseCAP ORCH S4



Features

- Air temperature/ humidity/ barometric pressure/ light all in one
- Universal protocols: MODBUS RS-485 or SDI-12
- High reliability and stability
- Wide range power supply: 3.6V ~ 16V
- Ultra-low power consumption
- Easy to use, integrate and install
- IP66 enclosure, suitable for outdoor applications
- Working in extreme compicate environment

Applications

- Smart Agriculture
- Smart Cities
- Smart Industry
- Environmental Monitoring
- Other Sensor Applications

Introduction

The SenseCAP ORCH S4 is designed for the professional environmental monitoring application. It measures and provides reliable data for the customers, even in extreme environmental conditions. The SenseCAP ORCH S4 provides four of the most important environmental parameters, which are air temperature, relative humidity, barometric pressure, and light intensity through a flexible combination.

It supports two standard protocols: MODBUS (MODBUS-RTU / MODBUS-ASCII) and SDI-12, with low power consumption and wide range power voltage from 3.6V to 16V. Built-in data pre-processing, therefore customers can quickly complete system development and integration.

The Solar Radiation Shield can effectively reduce the impact of solar radiation. which improve the accuracy of detection. The enclosure can protect the device from rain and sunlight exposure, etc.

Specifications

Air Temperature	
Range	-40 ℃ to +85 ℃
Accuracy	±0.2 °C
Resolution	0.1 ℃
Drift	< 0.03 °C /year
Air Humidity	
Range	0 to 100 %RH
Accuracy	±1.5 %RH
Resolution	1 %RH
Drift	< 0.25 %RH/year

Barometric Pressure			
Parameters	Condition	Value	
Range	-	300~1100 hPa	
Resolution	-	1 Pa	
Relative Accuracy	700 to 900 hPa 25 to 40 ℃	±0.12 hPa	
Absolute Accuracy	300 to 1100 hPa -20 to 0 ℃	±1.7 hPa	
Absolute Accuracy	300 to 1100 hPa 0 to 65 ℃	±1.0 hPa	
Temperature Coefficient Offset	900 hPa 25 to 40 °C	1.5 Pa/K	
Drift	-	±1.0 hPa/year	

ight Intensity	
Range	0 to 188000 Lux
Accuracy	± 5%
Resolution	0.045 Lux

SenseCAP ORCH S4

MODBUS RS-485	
Power Supply	3.6V ~ 16V
Current Consumption	Vin=16V: 3.6mA (typical) Vin=12V: 4.7mA (typical) Vin=5V: 11.0mA (typical) Vin=3.6V: 14.5mA (typical)
Warm-up Time	250ms (typical)
Scan Interval	1s
Poll Rate	1Hz
Response Time	≤ 4ms

3.6V ~ 16V

15ms

350ms (typical)

Vin=16V: 40.0µA (typical)

Vin=12V: 45.3µA (typical)

Vin=16V: 3.04mA (typical) Vin=12V: 3.98mA (typical)

Vin=5V: 8.85mA (typical)

Vin=3.6V: 11.80mA (typical)

Vin=5V: 77.6µA (typical) Vin=3.6V: 2.2mA (typical)

General Parameters Product Model SenseCAP ORCH S4 Microcontroller Ultra-low-power MCU RS-485 Interface MODBUS-RTU RS485/ MODBUS-ASCII Protocol RS485/ SDI-12 (v1.4) IP66 (water-proof box) IP Rating IPX5 (solar radiation shield) **Enclosure Material Engineering plastics** Operating Temperature -40 ℃ to +65 ℃ **Operating Humidity** 0 to 100 %RH (non-condensing) Cable Length 2 meters **Device Weight** 870g

Certification



SDI-12

Power Supply

(Sleep Mode)

Warm-up Time

Scan Interval

Current Consumption

Current Consumption (Active Mode)

Device Dimensions





Website: www.seeedstudio.com Email: iot@seeed.cc Phone: +86 755 3653 4305 Address: F9, Building G3, TCL International E City, Zhongshanyuan Road, Nanshan District, Shenzhen, China. © 2008-2020 Seeed Technology Co., Ltd. All rights reserved.