Power MOSFET 200 mA, 50 V

N-Channel SOT-23

Typical applications are DC-DC converters, power management in portable and battery-powered products such as computers, printers, PCMCIA cards, cellular and cordless telephones.

Features


- Low Threshold Voltage (V_{GS(th)}: 0.5 V–1.5 V) Makes it Ideal for Low Voltage Applications
- Miniature SOT-23 Surface Mount Package Saves Board Space
- BVSS Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free and are RoHS Compliant





ON Semiconductor®


http://onsemi.com

200 mA, 50 V









= Date Code*

= Pb-Free Package

(Note: Microdot may be in either location) *Date Code orientation and/or overbar may vary depending upon manufacturing location.

ORDERING INFORMATION

Device	Package	Shipping [†]
BSS138LT1G	SOT-23 (Pb-Free)	3000 / Tape & Reel
BVSS138LT1G	SOT-23 (Pb-Free)	3000 / Tape & Reel
BSS138LT3G	SOT-23 (Pb-Free)	10,000 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

MAXIMUM RATINGS (T_A = 25°C unless otherwise noted)

		,	
Rating	Symbol	Value	Unit
Drain-to-Source Voltage	V _{DSS}	50	Vdc
Gate-to-Source Voltage - Continuous	V _{GS}	± 20	Vdc
Drain Current – Continuous @ T _A = 25°C – Pulsed Drain Current (t _p ≤ 10 μs)	I _D I _{DM}	200 800	mA
Total Power Dissipation @ $T_A = 25^{\circ}C$	PD	225	mW
Operating and Storage Temperature Range	T _J , T _{stg}	– 55 to 150	°C
Thermal Resistance, Junction-to-Ambient	$R_{\theta JA}$	556	°C/W
Maximum Lead Temperature for Soldering Purposes, for 10 seconds	ΤL	260	°C


Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

ELECTRICAL CHARACTERISTICS ($T_A = 25^{\circ}C$ unless otherwise noted)

	Symbol	Min	Тур	Max	Unit	
OFF CHARACTERISTICS		•			•	
Drain-to-Source Breakdown V (V _{GS} = 0 Vdc, I _D = 250 μ Adc	V _{(BR)DSS}	50	-	-	Vdc	
$\label{eq:stars} \begin{array}{l} \mbox{Zero Gate Voltage Drain Curre} \\ (V_{DS} = 25 \mbox{ Vdc}, V_{GS} = 0 \mbox{ Vdc}, \\ (V_{DS} = 50 \mbox{ Vdc}, V_{GS} = 0 \mbox{ Vdc}, \\ (V_{DS} = 50 \mbox{ Vdc}, V_{GS} = 0 \mbox{ Vdc}, \\ \end{array}$	I _{DSS}	_ _ _	_ _ _	0.1 0.5 5.0	μAdc	
Gate-Source Leakage Current	I _{GSS}	-	-	±0.1	μAdc	
ON CHARACTERISTICS (Note	1)					
Gate-Source Threshold Voltag ($V_{DS} = V_{GS}$, $I_D = 1.0$ mAdc)	V _{GS(th)}	0.5	-	1.5	Vdc	
Static Drain-to-Source On-Resistance (V _{GS} = 2.75 Vdc, I_D < 200 mAdc, T_A = -40°C to +85°C) (V _{GS} = 5.0 Vdc, I_D = 200 mAdc)		r _{DS(on)}		5.6 _	10 3.5	Ω
Forward Transconductance $(V_{DS} = 25 \text{ Vdc}, I_D = 200 \text{ mAc}$	9 _{fs}	100	-	-	mmhos	
DYNAMIC CHARACTERISTICS		1				•
Input Capacitance	$(V_{DS} = 25 \text{ Vdc}, V_{GS} = 0, f = 1 \text{ MHz})$	C _{iss}	-	40	50	pF
Output Capacitance	$(V_{DS} = 25 \text{ Vdc}, V_{GS} = 0, f = 1 \text{ MHz})$	C _{oss}	-	12	25	
Transfer Capacitance	$(V_{DG} = 25 \text{ Vdc}, V_{GS} = 0, f = 1 \text{ MHz})$	C _{rss}	-	3.5	5.0	1
SWITCHING CHARACTERISTIC	CS (Note 2)	·	•	•	•	•
Turn-On Delay Time		t _{d(on)}	-	-	20	ns
Turn-Off Delay Time	(V _{DD} = 30 Vdc, I _D = 0.2 Adc,)	t _{d(off)}	_	_	20	

2. Switching characteristics are independent of operating junction temperature.

TYPICAL ELECTRICAL CHARACTERISTICS



TYPICAL ELECTRICAL CHARACTERISTICS






Figure 11. Body Diode Forward Voltage



PACKAGE DIMENSIONS

SOT-23 (TO-236) CASE 318-08 **ISSUE AP**





NOTES

DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982. 1. 2

CONTROLLING DIMENSION: INCH. MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH 3

THICKNESS. MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF BASE MATERIAL.

DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.


	MILLIMETERS			INCHES			
DIM	MIN	NOM	MAX	MIN	NOM	MAX	
Α	0.89	1.00	1.11	0.035	0.040	0.044	
A1	0.01	0.06	0.10	0.001	0.002	0.004	
b	0.37	0.44	0.50	0.015	0.018	0.020	
С	0.09	0.13	0.18	0.003	0.005	0.007	
D	2.80	2.90	3.04	0.110	0.114	0.120	
Е	1.20	1.30	1.40	0.047	0.051	0.055	
е	1.78	1.90	2.04	0.070	0.075	0.081	
L	0.10	0.20	0.30	0.004	0.008	0.012	
L1	0.35	0.54	0.69	0.014	0.021	0.029	
HE	2.10	2.40	2.64	0.083	0.094	0.104	
θ	0°		10°	0°		10°	

STYLE 21: PIN 1. GATE

2. SOURCE

З. DRAIN

SOLDERING FOOTPRINT*



*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and 💷 are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All or operating parameters, including "Typical" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications Buyer purchase or use SCILLC products for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

BSS138LT1/D