

# 2.5A, 3MHz Switching Charger with Dynamic Power Path Management

#### DESCRIPTION

ETAGOD3 is a switching Li-lon battery charger with dynamic power-path control and input current limiting. When a battery is connected, depending on the battery voltage, the DC-DC switching regulator either pre-conditions, fast-charges the battery or just regulates a system voltage ( $V_{SYS}$ ) to a preset voltage. It does not require an external sense resistor for current sensing. The charging current is determined by programming ISET1 or ISET2 pin, depending on the state of the USB\_DET. If USB\_DET is low, indicating an valid AC adapter input is present, the charge current is set by ISET1; otherwise, it is set by ISET2. When the battery voltage reaches the termination voltage i.e. 4.2V, the charging path disconnects SYS to BATT. The ETAGOD3 also includes a dynamic power path when the SYS load current exceeds current limit of the DCDC regulator internally set, the SYS voltage falls below  $V_{BATT}$ , ETAGOD3 turns on the power-path to supplement the system load through the battery.

#### FEATURES

- Switching Charger with Power Path Management
- Up to 95% DC-DC Efficiency
- 50mΩ Power Path MOSFET
- Up to 2.5A Max charging current
- Instant on with a dead Battery or no Battery
- No battery detection
- No External Sense resistor
- Programmable USB and AC IN Charging Current


### APPLICATIONS

- Tablet, MID
- Smart Phone
- Power Bank

#### ORDERING INFORMATION

PART	PACKAGE PIN	TOP MARK
ETA6003Q3Q	QFN3X3-16	ETA-42 – Product Number
		YWWPL - Date Code


### TYPICAL APPLICATION



2A Switching Charger with Dynamic Power Pat



### PIN CONFIGURATION



#### ABSOLUTEMAXIMUM RATINGS

(Note: Exceeding these limits may damage the device. Exposure to absolute maximum rating conditions for long periods may affect device reliability.)

IN, BATT Voltage	0.3V to 6V
All Other Pin Voltage	VIN-0.3V toVIN+0.3
SW,SYS,BATT to ground current	Internally limited
Operating Temperature Range	40°C to 85°
Storage Temperature Range	55°C to 150°C
Thermal Resistance	$\boldsymbol{\Theta}$ JA
QFN3X3-16	0C/W

### ELECTRICAL CHACRACTERISTICS

(V\_{IN} = 5V, unless otherwise specified. Typical values are at TA = 25oC.)

PARAMETER	CONDITIONS	MIN	ТҮР	MAX	UNITS
IN INPUT					
INPUT Range		4.4		5.5	۷
INPUT UVLO	Rising, Hys=500mV		4.35		۷
	Switcher Enable, Switching		5		mA
INPUT Operating Current	Switcher Enable, No Switching		70		μA
BATT to INPUT leakage Current	Input Floating		0	5	μA
DC-DC and SYS OUTPUT					
VSYSMIN	I <sub>SYS</sub> =1A, Default		3.6		V
VSYSMAX			4.5		V
Load Regulation			40		mV/A
Line Regulation	V <sub>IN</sub> =4.75 to 5.25V		0.04		%/V
Switching Frequency			3		MHz
Max duty		100			%

www.ETAsolution.com

**Outperform with Efficiency** 

2



PARAMETER	CONDITIONS	MIN	ТҮР	МАХ	UNITS
HIGHSIDE MOS RDSON	I <sub>sw</sub> =500mA		100		mΩ
LOWSIDE MOS RDSON	I <sub>sw</sub> =500mA		60		mΩ
HIGHSIDE Current limit			3.5		Α
SYS UVLO	Falling, Hys=200mV		2.25		٧
Thermal Shutdown	Rising, Hys=30°C		160		<u>л</u>
POWER PATH Management					•
BATT TO SYS RDSON			50		mΩ
BATTERY CHARGER					
Battery CV voltage	I <sub>BAT</sub> =OmA, default	4.16	4.2	4.24	۷
Charger Restart Threshold	From DONE to FastCharge		-200		тV
Battery Pre-condition Voltage	V <sub>BAT</sub> Rising Hys=180mV		2.9		۷
Pre-Condition Charge Current			100		mA
AC Fast Charge Current	R <sub>ISETI</sub> =500Ω, USB_DET= low lcharge=1V*1000/R <sub>ISETI</sub>		2		A
USB Charge Current	R <sub>ISETZ</sub> =2KΩ, USB_DET= high Icharge=1V*1000/R <sub>ISETZ</sub>		0.5		A
Pre-condition Timer			120		min
Fast-Charge Timer			960		min
THERMISTOR MONITOR					
NTC Threshold, Cold	Charger Suspended		76.5		%V <sub>IN</sub>
NTC Threshold, Hot	Charger Suspended		35		%V <sub>IN</sub>
NTC Threshold Hysteresis			1.5		%V <sub>IN</sub>
NTC Disable Threshold			100		тV
NTC Input Leakage			0		μA
LOGIC INPUT, STATS					
ENB Logic Input High		1.6			۷
ENB Logic Input Low				0.3	V
STAT Output Low Voltage	AmOr=10mA			0.2	۷

### PIN DESCRIPTION

PIN #	NAME	DESCRIPTION	
1,15	SAS	System Voltage Pin. It is also the Switching regulator's output pin. Connect an inductor and capacitor to form the output filter	
2	IN	Input pin. Can be connected to an AC adaptor or a USB charger output. Bypass with a $10 \mu F$ capacitor each to GND and PGND	
3,4	SM	Switching node of the Switching Regulator. Connect a 1 $\mu$ H to 2.2 $\mu$ H inductor from this pin to SYS	
5	PGND	Power Ground. Bypass with a 10 $\mu$ F capacitor to IN with a shortest possible trace	
6	ENB	Active Low Enable pin. Tie this pin low to enable the Charging, tie high to disable Charging, while	
		still keeping powerpath from BATT to SYS	

www.ETAsolution.com

Outperform with Efficiency


3



7	NTC	Thermistor input	
8,10	GND	Analog Ground Pin. Bypass with a 10 $\mu$ F capacitor to IN	
9	STATS	Status pin for Charging status indications. An open drain device capable of driving 10mA current	
11	ISETI	AC Fast Charge Current set pin for AC input. Connecting a Resistor between ISETI to GND This	
		sets the fast charge current value for AC adapter when USB_DET is low.	
12	ISET2	USB Charge Current set pin for USB input. Connecting a Resistor between ISET2 to GND This sets	
		the charge current value for USB input when USB_DET is high.	
13	USB_DET	Charge current selecting input. Pull this pin low if an AC adapter is connected and select fast	
		charging current to be set by ISETI. And set this pin high if a USB input is connected and select	
		USB charging current to be set by ISET2. It is default low.	
14,16	BATT	Battery pin. Connect a Battery to this pin	

#### TYPICAL CHARACTERISTICS

(Typical values are at  $T_{\text{A}}=25^{\circ}\text{C}$  unless otherwise specified.)



4







#### TYPICAL CHARACTERISTICS


(Typical values are at  $T_{\text{A}}$  = 25°C unless otherwise specified.)

#### **Battery Inserted During Detection**




#### **Battery Pulled During Charging**






V<sub>SYS</sub> Load Step Into Reduce Charging





50ms/div







V<sub>SYS</sub> Load Step Into IN DPPM Mode, IIN LIMIT=0.5A















#### TYPICAL APPLICATION





#### **PCB GUIDELINE**

PCB layout cautions of ETA6003 is shown below. The input capacitor (Cin) between Vin (Pin2) and PGND (Pin5) is always to be placed closest to the IC. SW wire can be laid through the gap between the 2 Cin terminals. It can go underneath the Cin. For all pins that needs to shorted to GND, please connect them to GND (Pin10), not to PGND (Pin5). A real PCB layout example is also listed below for reference.



www.ETAsolution.com

Outperform with Efficiency


6

**Proprietary Information DO NOT Distribute** 




### PACKAGE OUTLINE

Q



#### COMMON DIMENSIONS (UNITS OF MEASURE=MILLIMETER)

SYMBOL	MIN	NOM	MAX
A	0.70	0.75	0.80
A1	0	0.02	0.05
A3	0.20REF		
b	0.20	0.25	0.30
D	2.90	3.00	3.10
E	2.90	3.00	3.10
D2	1.55	1.65	1.75
E2	1.55	1.65	1.75
е	0.40	0.50	0.60
K	0.20	-	-
L	0.35	0.40	0.45
R	0.09	-	-



\_\_\_\_\_

NOTE: ALL DIMENSIONS REFER TO JEDEC STANDRAD MO-220 WEED-4.

www.ETAsolution.com